

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220938

Luminaire Tested: **9004-W1-FL-LED4080-S-WT-L3-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29496)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED4080-S-WT-L3-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, SPOT OPTIC, WHITE HOUSING.
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2801.3 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220938

CATALOG NUMBER: 9004-W1-FL-LED4080-S-WT-L3-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220938

CATALOG NUMBER: 9004-W1-FL-LED4080-S-WT-L3-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	104	103	101	100	99	98	98	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81
6	95	89	84	81	94	88	83	80	86	83	80	85	82	79	84	81	79	78
7	92	85	80	77	91	85	80	77	83	79	77	82	79	76	81	78	76	75
8	89	82	77	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72
9	87	79	75	72	86	79	74	71	78	74	71	77	74	71	76	73	71	70
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2169650
5°	1688861
10°	703395
15°	297406
20°	204112
25°	162908
30°	150546
35°	123172
40°	25924
45°	5931
50°	2111
55°	1720
60°	987
65°	584
70°	361
75°	477
80°	0
85°	0



TEST NUMBER: P220938

CATALOG NUMBER: 9004-W1-FL-LED4080-S-WT-L3-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1025.1	36.6
10°-20°	718.4	25.6
20°-30°	566.2	20.2
30°-40°	445.8	15.9
40°-50°	36.0	1.3
50°-60°	7.0	0.2
60°-70°	1.8	0.1
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2309.7	82.5
0°-40°	2755.5	98.4
0°-60°	2798.5	99.9
0°-90°	2801.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2801.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17590	
5°	13640	###
15°	2329	718
25°	1197	566
35°	818	446
45°	34	36
55°	8	7
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220938

CATALOG NUMBER: 9004-W1-FL-LED4080-S-WT-L3-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	17590
1°	17348
2°	16845
3°	16065
4°	14998
5°	13640
6°	12072
7°	10378
8°	8716
9°	7043
10°	5616
11°	4477
12°	3651
13°	3066
14°	2642
15°	2329
16°	2094
17°	1922
18°	1791
19°	1666
20°	1555
21°	1463
22°	1381
23°	1309
24°	1246
25°	1197
26°	1160
27°	1132
28°	1105
29°	1081
30°	1057
32.5°	997
35°	818
37.5°	488
40°	161
42.5°	48
45°	34
47.5°	24
50°	11
52.5°	10
55°	8
57.5°	6
60°	4
62.5°	2
65°	2



TEST NUMBER: P220938

CATALOG NUMBER: 9004-W1-FL-LED4080-S-WT-L3-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1
70°	1
72.5°	1
75°	1
77.5°	1
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)