

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P221018

Luminaire Tested: **9004-W1-FL-LED4080-W-WT-L3-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221018
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29499)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED4080-W-WT-L3-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, WIDE FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2790.2 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221018

CATALOG NUMBER: 9004-W1-FL-LED4080-W-WT-L3-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221018

CATALOG NUMBER: 9004-W1-FL-LED4080-W-WT-L3-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78	74	72	70
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74	70	67	65
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70	66	63	61
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66	62	59	57
9	75	66	60	56	74	65	60	56	64	59	56		63	59	55		63	58	55	54
10	72	62	56	53	71	62	56	52	61	56	52		60	55	52		59	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	391376
5°	398690
10°	386016
15°	355508
20°	304658
25°	259809
30°	222187
35°	166087
40°	58932
45°	27561
50°	18230
55°	12258
60°	6167
65°	1459
70°	1082
75°	953
80°	0
85°	0



TEST NUMBER: P221018

CATALOG NUMBER: 9004-W1-FL-LED4080-W-WT-L3-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	303.0	10.9
10°-20°	768.4	27.5
20°-30°	877.2	31.4
30°-40°	644.0	23.1
40°-50°	136.7	4.9
50°-60°	51.7	1.9
60°-70°	7.3	0.3
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1948.6	69.8
0°-40°	2592.5	92.9
0°-60°	2780.9	99.7
0°-90°	2790.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2790.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3173	
5°	3220	303
15°	2784	768
25°	1909	877
35°	1103	644
45°	158	137
55°	57	52
65°	5	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P221018

CATALOG NUMBER: 9004-W1-FL-LED4080-W-WT-L3-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	3173
1°	3172
2°	3180
3°	3196
4°	3211
5°	3220
6°	3218
7°	3201
8°	3168
9°	3127
10°	3082
11°	3031
12°	2979
13°	2920
14°	2856
15°	2784
16°	2702
17°	2611
18°	2517
19°	2418
20°	2321
21°	2231
22°	2144
23°	2062
24°	1984
25°	1909
26°	1836
27°	1762
28°	1691
29°	1625
30°	1560
32.5°	1385
35°	1103
37.5°	745
40°	366
42.5°	206
45°	158
47.5°	124
50°	95
52.5°	75
55°	57
57.5°	41
60°	25
62.5°	7
65°	5



TEST NUMBER: P221018

CATALOG NUMBER: 9004-W1-FL-LED4080-W-WT-L3-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	4
70°	3
72.5°	3
75°	2
77.5°	1
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)