

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220996

Luminaire Tested: **9004-W1-FL-LED4097-F-WT-L3-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220996
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29495)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED4097-F-WT-L3-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 4000K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2200.3 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220996

CATALOG NUMBER: 9004-W1-FL-LED4097-F-WT-L3-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220996

CATALOG NUMBER: 9004-W1-FL-LED4097-F-WT-L3-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	96	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	67	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	622501
5°	601514
10°	530014
15°	409255
20°	254057
25°	154960
30°	128512
35°	78436
40°	13284
45°	4849
50°	1075
55°	516
60°	395
65°	467
70°	289
75°	381
80°	0
85°	0



TEST NUMBER: P220996

CATALOG NUMBER: 9004-W1-FL-LED4097-F-WT-L3-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	443.8	20.2
10°-20°	858.2	39.0
20°-30°	558.9	25.4
30°-40°	310.4	14.1
40°-50°	24.3	1.1
50°-60°	2.6	0.1
60°-70°	1.5	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1860.8	84.6
0°-40°	2171.2	98.7
0°-60°	2198.1	99.9
0°-90°	2200.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2200.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5047	
5°	4858	444
15°	3205	858
25°	1139	559
35°	521	310
45°	28	24
55°	2	3
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P220996

CATALOG NUMBER: 9004-W1-FL-LED4097-F-WT-L3-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	5046.8
1°	5024.6
2°	4992.1
3°	4958.0
4°	4917.6
5°	4858.1
6°	4778.0
7°	4672.6
8°	4541.8
9°	4391.9
10°	4231.7
11°	4057.3
12°	3867.8
13°	3664.8
14°	3441.2
15°	3204.9
16°	2948.0
17°	2680.0
18°	2426.3
19°	2171.0
20°	1935.5
21°	1713.5
22°	1520.8
23°	1359.8
24°	1234.6
25°	1138.6
26°	1068.8
27°	1013.3
28°	969.7
29°	934.8
30°	902.3
32.5°	765.2
35°	520.9
37.5°	267.2
40°	82.5
42.5°	39.6
45°	27.8
47.5°	17.4
50°	5.6
52.5°	3.2
55°	2.4
57.5°	2.4
60°	1.6
62.5°	1.6
65°	1.6



TEST NUMBER: P220996

CATALOG NUMBER: 9004-W1-FL-LED4097-F-WT-L3-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.6
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)