

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P221579

Luminaire Tested: **9003-W2-FL-LED2797-S-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29476)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9003-W2-FL-LED2797-S-WT-L1-UNV
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, FLUSH LENS, SPOT OPTIC, WHITE HOUSING.
Light Source: (1) 2700K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1289.1 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 19.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221579

CATALOG NUMBER: 9003-W2-FL-LED2797-S-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221579

CATALOG NUMBER: 9003-W2-FL-LED2797-S-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		56	56	56	50
1	101	98	95	93	93	91	89	87	78	76	75		66	65	64		54	54	53	48
2	95	90	86	82	88	84	80	77	73	70	68		62	61	60		53	52	51	47
3	90	83	78	74	84	78	74	70	68	66	63		60	58	56		51	50	49	45
4	85	78	72	68	80	73	69	65	65	61	59		57	55	53		50	48	47	44
5	81	73	67	63	76	69	64	60	61	58	55		55	52	50		48	47	46	43
6	77	69	63	59	72	65	60	57	59	55	52		53	50	48		47	45	44	42
7	74	65	59	55	69	62	57	53	56	52	50		51	48	46		46	44	43	41
8	70	62	56	52	66	59	54	51	54	50	48		49	46	45		44	43	42	40
9	68	59	53	50	64	56	52	48	52	48	46		47	45	43		43	42	40	39
10	65	56	51	48	62	54	49	46	50	46	44		46	43	42		42	41	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1071690
5°	832069
10°	355460
15°	150307
20°	99642
25°	74690
30°	28612
35°	4363
40°	2376
45°	1054
50°	785
55°	726
60°	833
65°	778
70°	705
75°	678
80°	505
85°	1006



TEST NUMBER: P221579

CATALOG NUMBER: 9003-W2-FL-LED2797-S-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	285.7	22.2
10°-20°	202.4	15.7
20°-30°	130.5	10.1
30°-40°	18.8	1.5
40°-50°	3.0	0.2
50°-60°	1.8	0.1
60°-70°	1.4	0.1
70°-80°	0.7	0.1
80°-90°	0.3	0.0
90°-100°	0.3	0.0
100°-110°	0.7	0.1
110°-120°	1.4	0.1
120°-130°	1.8	0.1
130°-140°	3.0	0.2
140°-150°	18.8	1.5
150°-160°	130.5	10.1
160°-170°	202.4	15.7
170°-180°	285.7	22.2
0°-30°	618.6	48.0
0°-40°	637.4	49.4
0°-60°	642.2	49.8
0°-90°	644.6	50.0
90°-120°	2.4	0.2
90°-150°	26.0	2.0
90°-180°	645.0	50.0
0°-180°	1289.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4887	
5°	3780	286
15°	662	202
25°	309	130
35°	16	19
45°	3	3
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	0
95°	0	0
105°	1	1
115°	2	1
125°	2	2
135°	3	3
145°	16	19
155°	309	130
165°	662	202
175°	3780	286
180°	4887	



TEST NUMBER: P221579

CATALOG NUMBER: 9003-W2-FL-LED2797-S-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	4887.3
1°	4826.2
2°	4691.3
3°	4469.4
4°	4160.8
5°	3780.1
6°	3342.5
7°	2885.6
8°	2433.6
9°	1986.9
10°	1596.4
11°	1277.5
12°	1047.7
13°	879.7
14°	755.0
15°	662.1
16°	585.5
17°	529.7
18°	489.9
19°	455.0
20°	427.0
21°	402.7
22°	381.5
23°	361.7
24°	339.0
25°	308.7
26°	273.0
27°	234.7
28°	193.0
29°	151.7
30°	113.0
32.5°	37.5
35°	16.3
37.5°	11.8
40°	8.3
42.5°	4.2
45°	3.4
47.5°	2.7
50°	2.3
52.5°	2.3
55°	1.9
57.5°	1.9
60°	1.9
62.5°	1.5
65°	1.5



TEST NUMBER: P221579

CATALOG NUMBER: 9003-W2-FL-LED2797-S-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.1
70°	1.1
72.5°	0.8
75°	0.8
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.4
97.5°	0.4
100°	0.4
102.5°	0.4
105°	0.8
107.5°	0.8
110°	1.1
112.5°	1.1
115°	1.5
117.5°	1.5
120°	1.9
122.5°	1.9
125°	1.9
127.5°	2.3
130°	2.3
132.5°	2.7
135°	3.4
137.5°	4.2
140°	8.3
142.5°	11.8
145°	16.3
147.5°	37.5
150°	113.0
151°	151.7
152°	193.0
153°	234.7
154°	273.0
155°	308.7
156°	339.0
157°	361.7
158°	381.5
159°	402.7
160°	427.0
161°	455.0



TEST NUMBER: P221579

CATALOG NUMBER: 9003-W2-FL-LED2797-S-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
162°	489.9
163°	529.7
164°	585.5
165°	662.1
166°	755.0
167°	879.7
168°	1047.7
169°	1277.5
170°	1596.4
171°	1986.9
172°	2433.6
173°	2885.6
174°	3342.5
175°	3780.1
176°	4160.8
177°	4469.4
178°	4691.3
179°	4826.2
180°	4887.3

(END OF REPORT)