

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P221875

Luminaire Tested: **9004-W2-[RW, RI]-LED4080-M-WT-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221875
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29488)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W2-[RW, RI]-LED4080-M-WT-L2-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4087.7 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221875

CATALOG NUMBER: 9004-W2-[RW, RI]-LED4080-M-WT-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221875

CATALOG NUMBER: 9004-W2-[RW, RI]-LED4080-M-WT-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 107 | 107 | 107 | 107 | 99 | 99 | 99 | 99 | 83 | 83 | 83 | 69 | 69 | 69 | 56 | 56 | 56 | 50 |
| 1 | 100 | 97 | 94 | 92 | 93 | 90 | 88 | 85 | 77 | 75 | 74 | 65 | 64 | 63 | 54 | 53 | 52 | 47 |
| 2 | 94 | 89 | 84 | 80 | 87 | 83 | 79 | 75 | 71 | 69 | 66 | 61 | 59 | 58 | 51 | 50 | 49 | 45 |
| 3 | 88 | 81 | 76 | 72 | 82 | 76 | 72 | 68 | 67 | 63 | 61 | 57 | 55 | 53 | 49 | 48 | 47 | 43 |
| 4 | 83 | 75 | 69 | 65 | 78 | 71 | 66 | 62 | 62 | 59 | 56 | 54 | 52 | 50 | 47 | 46 | 44 | 41 |
| 5 | 79 | 70 | 64 | 59 | 73 | 66 | 61 | 57 | 59 | 55 | 52 | 52 | 49 | 47 | 45 | 44 | 42 | 39 |
| 6 | 75 | 65 | 59 | 55 | 70 | 62 | 57 | 53 | 55 | 51 | 48 | 49 | 46 | 44 | 44 | 42 | 40 | 38 |
| 7 | 71 | 61 | 55 | 51 | 66 | 58 | 53 | 49 | 53 | 49 | 46 | 47 | 44 | 42 | 42 | 40 | 39 | 36 |
| 8 | 67 | 58 | 52 | 48 | 63 | 55 | 50 | 46 | 50 | 46 | 43 | 45 | 42 | 40 | 41 | 39 | 37 | 35 |
| 9 | 64 | 55 | 49 | 45 | 60 | 52 | 47 | 44 | 48 | 44 | 41 | 43 | 40 | 38 | 39 | 37 | 36 | 34 |
| 10 | 61 | 52 | 46 | 43 | 58 | 50 | 45 | 41 | 46 | 42 | 39 | 42 | 39 | 37 | 38 | 36 | 34 | 33 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 888570 |
| 5° | 814838 |
| 10° | 597936 |
| 15° | 350208 |
| 20° | 191078 |
| 25° | 136138 |
| 30° | 100696 |
| 35° | 14531 |
| 40° | 7954 |
| 45° | 5652 |
| 50° | 5776 |
| 55° | 5978 |
| 60° | 6661 |
| 65° | 7442 |
| 70° | 8619 |
| 75° | 10675 |
| 80° | 12644 |
| 85° | 12029 |



TEST NUMBER: P221875

CATALOG NUMBER: 9004-W2-[RW, RI]-LED4080-M-WT-L2-UNV

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 569.6 | 13.9 |
| 10°-20° | 762.6 | 18.7 |
| 20°-30° | 470.8 | 11.5 |
| 30°-40° | 131.2 | 3.2 |
| 40°-50° | 26.5 | 0.6 |
| 50°-60° | 25.3 | 0.6 |
| 60°-70° | 25.4 | 0.6 |
| 70°-80° | 22.9 | 0.6 |
| 80°-90° | 9.6 | 0.2 |
| 90°-100° | 9.6 | 0.2 |
| 100°-110° | 22.9 | 0.6 |
| 110°-120° | 25.4 | 0.6 |
| 120°-130° | 25.3 | 0.6 |
| 130°-140° | 26.5 | 0.6 |
| 140°-150° | 131.2 | 3.2 |
| 150°-160° | 470.8 | 11.5 |
| 160°-170° | 762.6 | 18.7 |
| 170°-180° | 569.6 | 13.9 |
| 0°-30° | 1802.9 | 44.1 |
| 0°-40° | 1934.2 | 47.3 |
| 0°-60° | 1986.0 | 48.6 |
| 0°-90° | 2043.8 | 50.0 |
| 90°-120° | 57.9 | 1.4 |
| 90°-150° | 240.9 | 5.9 |
| 90°-180° | 2044.0 | 50.0 |
| 0°-180° | 4087.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|------|------|------|
| 0° | 7204 | |
| 5° | 6581 | 570 |
| 15° | 2742 | 763 |
| 25° | 1000 | 471 |
| 35° | 96 | 131 |
| 45° | 32 | 27 |
| 55° | 28 | 25 |
| 65° | 26 | 25 |
| 75° | 22 | 23 |
| 85° | 8 | 9 |
| 90° | 0 | 1 |
| 95° | 8 | 9 |
| 105° | 22 | 23 |
| 115° | 26 | 25 |
| 125° | 28 | 25 |
| 135° | 32 | 27 |
| 145° | 96 | 131 |
| 155° | 1000 | 471 |
| 165° | 2742 | 763 |
| 175° | 6581 | 570 |
| 180° | 7204 | |



TEST NUMBER: P221875

CATALOG NUMBER: 9004-W2-[RW, RI]-LED4080-M-WT-L2-UNV

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 7203.9 |
| 1° | 7159.1 |
| 2° | 7076.5 |
| 3° | 6959.2 |
| 4° | 6797.9 |
| 5° | 6581.0 |
| 6° | 6312.4 |
| 7° | 5992.8 |
| 8° | 5611.5 |
| 9° | 5201.6 |
| 10° | 4774.0 |
| 11° | 4338.7 |
| 12° | 3908.8 |
| 13° | 3489.6 |
| 14° | 3100.6 |
| 15° | 2742.5 |
| 16° | 2412.9 |
| 17° | 2117.2 |
| 18° | 1857.9 |
| 19° | 1636.4 |
| 20° | 1455.7 |
| 21° | 1306.8 |
| 22° | 1194.9 |
| 23° | 1110.0 |
| 24° | 1046.7 |
| 25° | 1000.3 |
| 26° | 962.5 |
| 27° | 929.3 |
| 28° | 897.7 |
| 29° | 826.7 |
| 30° | 707.0 |
| 32.5° | 342.7 |
| 35° | 96.5 |
| 37.5° | 66.4 |
| 40° | 49.4 |
| 42.5° | 34.7 |
| 45° | 32.4 |
| 47.5° | 30.9 |
| 50° | 30.1 |
| 52.5° | 28.6 |
| 55° | 27.8 |
| 57.5° | 27.8 |
| 60° | 27.0 |
| 62.5° | 27.0 |
| 65° | 25.5 |

TEST NUMBER: P221875

CATALOG NUMBER: 9004-W2-[RW, RI]-LED4080-M-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

| | 0° |
|--------|--------|
| 67.5° | 24.7 |
| 70° | 23.9 |
| 72.5° | 23.2 |
| 75° | 22.4 |
| 77.5° | 20.1 |
| 80° | 17.8 |
| 82.5° | 13.9 |
| 85° | 8.5 |
| 87.5° | 3.9 |
| 90° | 0.0 |
| 92.5° | 3.9 |
| 95° | 8.5 |
| 97.5° | 13.9 |
| 100° | 17.8 |
| 102.5° | 20.1 |
| 105° | 22.4 |
| 107.5° | 23.2 |
| 110° | 23.9 |
| 112.5° | 24.7 |
| 115° | 25.5 |
| 117.5° | 27.0 |
| 120° | 27.0 |
| 122.5° | 27.8 |
| 125° | 27.8 |
| 127.5° | 28.6 |
| 130° | 30.1 |
| 132.5° | 30.9 |
| 135° | 32.4 |
| 137.5° | 34.7 |
| 140° | 49.4 |
| 142.5° | 66.4 |
| 145° | 96.5 |
| 147.5° | 342.7 |
| 150° | 707.0 |
| 151° | 826.7 |
| 152° | 897.7 |
| 153° | 929.3 |
| 154° | 962.5 |
| 155° | 1000.3 |
| 156° | 1046.7 |
| 157° | 1110.0 |
| 158° | 1194.9 |
| 159° | 1306.8 |
| 160° | 1455.7 |
| 161° | 1636.4 |



TEST NUMBER: P221875

CATALOG NUMBER: 9004-W2-[RW, RI]-LED4080-M-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

| | 0° |
|------|--------|
| 162° | 1857.9 |
| 163° | 2117.2 |
| 164° | 2412.9 |
| 165° | 2742.5 |
| 166° | 3100.6 |
| 167° | 3489.6 |
| 168° | 3908.8 |
| 169° | 4338.7 |
| 170° | 4774.0 |
| 171° | 5201.6 |
| 172° | 5611.5 |
| 173° | 5992.8 |
| 174° | 6312.4 |
| 175° | 6581.0 |
| 176° | 6797.9 |
| 177° | 6959.2 |
| 178° | 7076.5 |
| 179° | 7159.1 |
| 180° | 7203.9 |

(END OF REPORT)