

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220845

Luminaire Tested: **9004-W1-[RW, RI]-LED3097-M-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220845  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29492)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-[RW, RI]-LED3097-M-BK-L1-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 3000K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 730.3 lumens  
Efficiency: N/A  
Efficacy: 74.5 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220845

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220845

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79
7	93	86	82	79	92	86	81	78	85	81	78	84	80	78	83	80	77	76
8	90	83	79	76	89	83	78	76	82	78	75	81	77	75	80	77	75	74
9	88	80	76	73	87	80	76	73	79	75	73	78	75	72	78	75	72	71
10	85	78	73	70	84	77	73	70	77	73	70	76	73	70	75	72	70	69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	335488
5°	307809
10°	227100
15°	132562
20°	71879
25°	50805
30°	36817
35°	4578
40°	1562
45°	611
50°	403
55°	323
60°	222
65°	175
70°	108
75°	143
80°	213
85°	0



TEST NUMBER: P220845

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	215.5	29.5
10°-20°	289.1	39.6
20°-30°	175.4	24.0
30°-40°	44.9	6.1
40°-50°	3.2	0.4
50°-60°	1.3	0.2
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	680.0	93.1
0°-40°	724.8	99.3
0°-60°	729.3	99.9
0°-90°	730.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	730.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2720	
5°	2486	216
15°	1038	289
25°	373	175
35°	30	45
45°	4	3
55°	2	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220845

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2719.9
1°	2702.5
2°	2671.6
3°	2627.3
4°	2566.8
5°	2486.0
6°	2385.0
7°	2271.4
8°	2126.3
9°	1971.4
10°	1813.2
11°	1646.8
12°	1483.3
13°	1326.9
14°	1176.7
15°	1038.1
16°	914.1
17°	802.3
18°	702.6
19°	618.5
20°	547.6
21°	491.9
22°	447.6
23°	414.9
24°	391.6
25°	373.3
26°	358.5
27°	345.8
28°	330.8
29°	303.3
30°	258.5
32.5°	123.0
35°	30.4
37.5°	16.5
40°	9.7
42.5°	4.4
45°	3.5
47.5°	3.0
50°	2.1
52.5°	1.8
55°	1.5
57.5°	1.2
60°	0.9
62.5°	0.9
65°	0.6



TEST NUMBER: P220845

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)