

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220815

Luminaire Tested: **9004-W1-[RW, RI]-LED3590-S-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220815  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29491)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-[RW, RI]-LED3590-S-BK-L1-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC, BLACK HOUSING.  
Light Source: (1) 3500K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 838.6 lumens  
Efficiency: N/A  
Efficacy: 85.6 lumens/watt  
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220815  
CATALOG NUMBER: 9004-W1-[RW, RI]-LED3590-S-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220815

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3590-S-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	99	97	106	102	98	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	95	89	85	82	87	84	82	86	83	81	86	83	81	80
8	93	86	82	80	92	86	82	79	85	82	79	84	81	79	83	81	78	78
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	81	79	76	75
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	79	77	74	74

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	737940
5°	576540
10°	242844
15°	102911
20°	69687
25°	55323
30°	40962
35°	3719
40°	1353
45°	419
50°	326
55°	366
60°	247
65°	204
70°	108
75°	143
80°	213
85°	0



TEST NUMBER: P220815

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3590-S-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	350.5	41.8
10°-20°	247.7	29.5
20°-30°	189.1	22.6
30°-40°	46.4	5.5
40°-50°	2.5	0.3
50°-60°	1.4	0.2
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.3	93.9
0°-40°	833.7	99.4
0°-60°	837.5	99.9
0°-90°	838.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	838.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5983	
5°	4656	351
15°	806	248
25°	406	189
35°	25	46
45°	2	2
55°	2	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220815

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3590-S-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5982.7
1°	5906.0
2°	5737.1
3°	5477.9
4°	5115.0
5°	4656.4
6°	4129.3
7°	3550.1
8°	2966.9
9°	2433.0
10°	1938.9
11°	1547.6
12°	1261.1
13°	1058.3
14°	914.1
15°	805.9
16°	722.8
17°	662.3
18°	614.3
19°	569.4
20°	530.9
22.5°	457.9
25°	406.5
26°	392.7
27°	381.2
28°	369.7
29°	339.3
30°	287.6
32.5°	129.4
35°	24.7
37.5°	13.5
40°	8.4
42.5°	3.7
45°	2.4
47.5°	2.0
50°	1.7
52.5°	1.7
55°	1.7
57.5°	1.4
60°	1.0
62.5°	1.0
65°	0.7
67.5°	0.3
70°	0.3
72.5°	0.3



TEST NUMBER: P220815

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3590-S-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)