

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220997

Luminaire Tested: **9004-W1-FL-LED2790-W-WT-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220997  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29499)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED2790-W-WT-L1-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, WIDE FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 2700K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 880.0 lumens  
Efficiency: N/A  
Efficacy: 89.8 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.91  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220997

CATALOG NUMBER: 9004-W1-FL-LED2790-W-WT-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220997

CATALOG NUMBER: 9004-W1-FL-LED2790-W-WT-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57
9	75	66	60	56	74	65	60	56	64	59	56	63	59	55	63	58	55	54
10	72	62	56	53	71	62	56	52	61	56	52	60	55	52	59	55	52	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	123432
5°	125736
10°	121741
15°	112118
20°	96084
25°	81944
30°	70074
35°	52386
40°	18581
45°	8687
50°	5757
55°	3871
60°	1949
65°	467
70°	325
75°	286
80°	0
85°	0



TEST NUMBER: P220997

CATALOG NUMBER: 9004-W1-FL-LED2790-W-WT-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.6	10.9
10°-20°	242.3	27.5
20°-30°	276.6	31.4
30°-40°	203.1	23.1
40°-50°	43.1	4.9
50°-60°	16.3	1.9
60°-70°	2.3	0.3
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	614.5	69.8
0°-40°	817.6	92.9
0°-60°	877.1	99.7
0°-90°	880.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	880.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1001	
5°	1016	96
15°	878	242
25°	602	277
35°	348	203
45°	50	43
55°	18	16
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220997

CATALOG NUMBER: 9004-W1-FL-LED2790-W-WT-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1000.7
1°	1000.4
2°	1002.9
3°	1008.0
4°	1012.7
5°	1015.5
6°	1014.9
7°	1009.5
8°	999.1
9°	986.2
10°	972.0
11°	955.9
12°	939.5
13°	920.9
14°	900.7
15°	878.0
16°	852.2
17°	823.5
18°	793.8
19°	762.6
20°	732.0
21°	703.6
22°	676.2
23°	650.3
24°	625.7
25°	602.1
26°	579.0
27°	555.7
28°	533.3
29°	512.5
30°	492.0
32.5°	436.8
35°	347.9
37.5°	235.0
40°	115.4
42.5°	65.0
45°	49.8
47.5°	39.1
50°	30.0
52.5°	23.7
55°	18.0
57.5°	12.9
60°	7.9
62.5°	2.2
65°	1.6



TEST NUMBER: P220997

CATALOG NUMBER: 9004-W1-FL-LED2790-W-WT-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.3
70°	0.9
72.5°	0.9
75°	0.6
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)