

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220998

Luminaire Tested: **9004-W1-FL-LED3090-W-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220998
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29499)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED3090-W-WT-L1-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, WIDE FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 930.8 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220998

CATALOG NUMBER: 9004-W1-FL-LED3090-W-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220998

CATALOG NUMBER: 9004-W1-FL-LED3090-W-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78	74	72	70
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74	70	67	65
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70	66	63	61
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66	62	59	57
9	75	66	60	56	74	65	60	56	64	59	56		63	59	55		63	58	55	54
10	72	62	56	53	71	62	56	52	61	56	52		60	55	52		59	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	130574
5°	133016
10°	128780
15°	118605
20°	101636
25°	86680
30°	74133
35°	55412
40°	19660
45°	9193
50°	6083
55°	4086
60°	2048
65°	496
70°	361
75°	334
80°	0
85°	0



TEST NUMBER: P220998

CATALOG NUMBER: 9004-W1-FL-LED3090-W-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.1	10.9
10°-20°	256.4	27.5
20°-30°	292.6	31.4
30°-40°	214.8	23.1
40°-50°	45.6	4.9
50°-60°	17.2	1.9
60°-70°	2.4	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	650.1	69.8
0°-40°	864.9	92.9
0°-60°	927.7	99.7
0°-90°	930.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	930.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1059	
5°	1074	101
15°	929	256
25°	637	293
35°	368	215
45°	53	46
55°	19	17
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220998

CATALOG NUMBER: 9004-W1-FL-LED3090-W-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	1058.6
1°	1058.3
2°	1060.9
3°	1066.3
4°	1071.3
5°	1074.3
6°	1073.6
7°	1067.9
8°	1056.9
9°	1043.2
10°	1028.2
11°	1011.2
12°	993.9
13°	974.2
14°	952.8
15°	928.8
16°	901.4
17°	871.1
18°	839.7
19°	806.7
20°	774.3
21°	744.3
22°	715.3
23°	687.9
24°	661.9
25°	636.9
26°	612.5
27°	587.8
28°	564.2
29°	542.1
30°	520.5
32.5°	462.1
35°	368.0
37.5°	248.5
40°	122.1
42.5°	68.7
45°	52.7
47.5°	41.4
50°	31.7
52.5°	25.0
55°	19.0
57.5°	13.7
60°	8.3
62.5°	2.3
65°	1.7



TEST NUMBER: P220998

CATALOG NUMBER: 9004-W1-FL-LED3090-W-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.3
70°	1.0
72.5°	1.0
75°	0.7
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)