

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220924

Luminaire Tested: **9004-W1-FL-LED3597-S-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220924
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29496)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED3597-S-WT-L1-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, SPOT OPTIC, WHITE HOUSING.
Light Source: (1) 3500K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 937.5 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220924

CATALOG NUMBER: 9004-W1-FL-LED3597-S-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220924

CATALOG NUMBER: 9004-W1-FL-LED3597-S-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	104	103	101	100	99	98	98	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81
6	95	89	84	81	94	88	83	80	86	83	80	85	82	79	84	81	79	78
7	92	85	80	77	91	85	80	77	83	79	77	82	79	76	81	78	76	75
8	89	82	77	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72
9	87	79	75	72	86	79	74	71	78	74	71	77	74	71	76	73	71	70
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	726160
5°	565248
10°	235417
15°	99540
20°	68309
25°	54520
30°	50391
35°	41228
40°	8679
45°	1989
50°	710
55°	581
60°	321
65°	204
70°	108
75°	143
80°	0
85°	0



TEST NUMBER: P220924

CATALOG NUMBER: 9004-W1-FL-LED3597-S-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.1	36.6
10°-20°	240.4	25.6
20°-30°	189.5	20.2
30°-40°	149.2	15.9
40°-50°	12.1	1.3
50°-60°	2.3	0.2
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	773.0	82.5
0°-40°	922.2	98.4
0°-60°	936.6	99.9
0°-90°	937.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	937.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5887	
5°	4565	343
15°	780	240
25°	401	190
35°	274	149
45°	11	12
55°	3	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220924

CATALOG NUMBER: 9004-W1-FL-LED3597-S-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	5887.2
1°	5806.2
2°	5637.8
3°	5376.8
4°	5019.7
5°	4565.2
6°	4040.4
7°	3473.4
8°	2917.1
9°	2357.2
10°	1879.6
11°	1498.4
12°	1221.9
13°	1026.2
14°	884.2
15°	779.5
16°	700.8
17°	643.3
18°	599.4
19°	557.6
20°	520.4
21°	489.6
22°	462.2
23°	438.1
24°	417.0
25°	400.6
26°	388.2
27°	378.9
28°	369.8
29°	361.8
30°	353.8
32.5°	333.7
35°	273.8
37.5°	163.3
40°	53.9
42.5°	16.1
45°	11.4
47.5°	8.0
50°	3.7
52.5°	3.3
55°	2.7
57.5°	2.0
60°	1.3
62.5°	0.7
65°	0.7



TEST NUMBER: P220924

CATALOG NUMBER: 9004-W1-FL-LED3597-S-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)