

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P221079

Luminaire Tested: **9004-W1-FL-LED4080-F-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P221079  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29498)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED4080-F-BK-L1-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 4000K CCT, 80 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1200.1 lumens  
Efficiency: N/A  
Efficacy: 122.5 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.56  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P221079  
CATALOG NUMBER: 9004-W1-FL-LED4080-F-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P221079

CATALOG NUMBER: 9004-W1-FL-LED4080-F-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	107	104	100	98	100	98	96		97	95	94		95	93	92	90
3	105	99	95	92	103	98	94	91	96	92	90		93	90	88		91	89	87	85
4	101	94	89	86	99	93	89	85	91	87	84		89	86	83		87	85	82	81
5	97	89	84	81	95	88	84	80	87	83	80		85	82	79		84	81	78	77
6	93	85	80	76	91	84	79	76	83	79	75		82	78	75		80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	72		78	74	71		77	74	71	70
8	86	77	72	69	84	77	72	69	76	71	68		75	71	68		74	70	68	67
9	82	74	69	65	81	74	69	65	73	68	65		72	68	65		71	67	65	64
10	79	71	66	63	78	70	66	62	70	65	62		69	65	62		68	65	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	329123
5°	317862
10°	279855
15°	214965
20°	132955
25°	82379
30°	68650
35°	54946
40°	11980
45°	2547
50°	480
55°	280
60°	197
65°	117
70°	144
75°	191
80°	0
85°	0



TEST NUMBER: P221079

CATALOG NUMBER: 9004-W1-FL-LED4080-F-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	234.4	19.5
10°-20°	451.4	37.6
20°-30°	296.5	24.7
30°-40°	199.9	16.7
40°-50°	15.8	1.3
50°-60°	1.1	0.1
60°-70°	0.5	0.0
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	982.4	81.9
0°-40°	1182.3	98.5
0°-60°	1199.2	99.9
0°-90°	1200.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1200.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2668	
5°	2567	234
15°	1683	451
25°	605	296
35°	365	200
45°	15	16
55°	1	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P221079

CATALOG NUMBER: 9004-W1-FL-LED4080-F-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2668.3
1°	2656.6
2°	2639.5
3°	2620.7
4°	2598.5
5°	2567.2
6°	2524.1
7°	2468.1
8°	2399.1
9°	2319.3
10°	2234.4
11°	2141.2
12°	2039.6
13°	1928.8
14°	1810.9
15°	1683.4
16°	1549.3
17°	1410.5
18°	1271.7
19°	1141.2
20°	1012.9
21°	901.7
22°	801.8
23°	719.0
24°	655.1
25°	605.3
26°	569.4
27°	541.8
28°	518.4
29°	499.1
30°	482.0
32.5°	446.0
35°	364.9
37.5°	217.0
40°	74.4
42.5°	22.2
45°	14.6
47.5°	9.2
50°	2.5
52.5°	1.3
55°	1.3
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.4



TEST NUMBER: P221079

CATALOG NUMBER: 9004-W1-FL-LED4080-F-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)