

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220925

Luminaire Tested: **9004-W1-FL-LED4097-S-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220925
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29496)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED4097-S-WT-L1-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, SPOT OPTIC,
WHITE HOUSING.
Light Source: (1) 4000K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 928.5 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220925

CATALOG NUMBER: 9004-W1-FL-LED4097-S-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220925

CATALOG NUMBER: 9004-W1-FL-LED4097-S-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	104		103	101	100		99	98	98	96
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87	84	82	81
6	95	89	84	81	94	88	83	80	86	83	80		85	82	79		84	81	79	78
7	92	85	80	77	91	85	80	77	83	79	77		82	79	76		81	78	76	75
8	89	82	77	74	88	82	77	74	81	77	74		80	76	74		79	76	73	72
9	87	79	75	72	86	79	74	71	78	74	71		77	74	71		76	73	71	70
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74	71	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	719167
5°	559800
10°	233150
15°	98582
20°	67652
25°	54003
30°	49907
35°	40821
40°	8598
45°	1971
50°	691
55°	581
60°	321
65°	204
70°	108
75°	143
80°	0
85°	0



TEST NUMBER: P220925

CATALOG NUMBER: 9004-W1-FL-LED4097-S-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.8	36.6
10°-20°	238.1	25.6
20°-30°	187.7	20.2
30°-40°	147.8	15.9
40°-50°	11.9	1.3
50°-60°	2.3	0.3
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	765.6	82.5
0°-40°	913.4	98.4
0°-60°	927.6	99.9
0°-90°	928.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	928.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5830	
5°	4521	340
15°	772	238
25°	397	188
35°	271	148
45°	11	12
55°	3	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220925

CATALOG NUMBER: 9004-W1-FL-LED4097-S-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	5830.5
1°	5750.3
2°	5583.5
3°	5325.0
4°	4971.3
5°	4521.2
6°	4001.4
7°	3439.9
8°	2889.0
9°	2334.5
10°	1861.5
11°	1484.0
12°	1210.2
13°	1016.3
14°	875.7
15°	772.0
16°	694.1
17°	637.1
18°	593.7
19°	552.2
20°	515.4
21°	484.9
22°	457.8
23°	433.9
24°	413.0
25°	396.8
26°	384.5
27°	375.2
28°	366.3
29°	358.3
30°	350.4
32.5°	330.5
35°	271.1
37.5°	161.8
40°	53.4
42.5°	15.9
45°	11.3
47.5°	8.0
50°	3.6
52.5°	3.3
55°	2.7
57.5°	2.0
60°	1.3
62.5°	0.7
65°	0.7



TEST NUMBER: P220925

CATALOG NUMBER: 9004-W1-FL-LED4097-S-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)