

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220975

Luminaire Tested: **9004-W1-FL-LED5080-F-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29495)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED5080-F-WT-L1-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 5000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1205.1 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220975

CATALOG NUMBER: 9004-W1-FL-LED5080-F-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220975

CATALOG NUMBER: 9004-W1-FL-LED5080-F-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	96	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	67	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	340952
5°	329452
10°	290288
15°	224146
20°	139151
25°	84870
30°	70388
35°	42960
40°	7278
45°	2651
50°	576
55°	280
60°	222
65°	263
70°	144
75°	191
80°	0
85°	0



TEST NUMBER: P220975

CATALOG NUMBER: 9004-W1-FL-LED5080-F-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.1	20.2
10°-20°	470.0	39.0
20°-30°	306.1	25.4
30°-40°	170.0	14.1
40°-50°	13.3	1.1
50°-60°	1.4	0.1
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1019.2	84.6
0°-40°	1189.2	98.7
0°-60°	1203.9	99.9
0°-90°	1205.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1205.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2764	
5°	2661	243
15°	1755	470
25°	624	306
35°	285	170
45°	15	13
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220975

CATALOG NUMBER: 9004-W1-FL-LED5080-F-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2764.2
1°	2752.0
2°	2734.2
3°	2715.5
4°	2693.4
5°	2660.8
6°	2616.9
7°	2559.2
8°	2487.5
9°	2405.4
10°	2317.7
11°	2222.2
12°	2118.4
13°	2007.2
14°	1884.8
15°	1755.3
16°	1614.6
17°	1467.8
18°	1328.9
19°	1189.0
20°	1060.1
21°	938.5
22°	832.9
23°	744.8
24°	676.2
25°	623.6
26°	585.4
27°	555.0
28°	531.1
29°	512.0
30°	494.2
32.5°	419.1
35°	285.3
37.5°	146.4
40°	45.2
42.5°	21.7
45°	15.2
47.5°	9.6
50°	3.0
52.5°	1.7
55°	1.3
57.5°	1.3
60°	0.9
62.5°	0.9
65°	0.9



TEST NUMBER: P220975

CATALOG NUMBER: 9004-W1-FL-LED5080-F-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.9
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)