

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220948

Luminaire Tested: **9004-W1-FL-LED5080-M-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29497)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED5080-M-WT-L1-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 5000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1227.3 lumens
Efficiency: N/A
Efficacy: 125.2 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220948

CATALOG NUMBER: 9004-W1-FL-LED5080-M-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220948

CATALOG NUMBER: 9004-W1-FL-LED5080-M-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86
4	101	95	91	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82
5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78
6	94	86	82	78	92	86	81	78	84	80	77	83	79	77	82	79	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	495319
5°	454519
10°	333962
15°	194431
20°	106020
25°	75357
30°	67909
35°	53485
40°	11883
45°	3262
50°	1075
55°	645
60°	419
65°	263
70°	144
75°	191
80°	0
85°	0



TEST NUMBER: P220948

CATALOG NUMBER: 9004-W1-FL-LED5080-M-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.0	25.9
10°-20°	424.4	34.6
20°-30°	265.4	21.6
30°-40°	196.9	16.0
40°-50°	18.3	1.5
50°-60°	2.9	0.2
60°-70°	1.0	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1007.8	82.1
0°-40°	1204.7	98.2
0°-60°	1225.9	99.9
0°-90°	1227.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1227.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4016	
5°	3671	318
15°	1523	424
25°	554	265
35°	355	197
45°	19	18
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220948

CATALOG NUMBER: 9004-W1-FL-LED5080-M-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	4015.7
1°	3989.2
2°	3944.1
3°	3878.9
4°	3789.5
5°	3670.9
6°	3523.7
7°	3346.1
8°	3138.9
9°	2907.9
10°	2666.4
11°	2419.3
12°	2180.1
13°	1946.8
14°	1725.4
15°	1522.6
16°	1338.0
17°	1176.9
18°	1032.3
19°	909.8
20°	807.7
21°	727.0
22°	662.3
23°	614.5
24°	579.3
25°	553.7
26°	534.6
27°	518.1
28°	502.9
29°	489.9
30°	476.8
32.5°	440.8
35°	355.2
37.5°	215.0
40°	73.8
42.5°	25.6
45°	18.7
47.5°	13.5
50°	5.6
52.5°	4.3
55°	3.0
57.5°	2.2
60°	1.7
62.5°	1.3
65°	0.9



TEST NUMBER: P220948

CATALOG NUMBER: 9004-W1-FL-LED5080-M-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.9
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)