

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P247023

Luminaire Tested: **203-SS-8LED2725-12-CS-LSL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247023  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-41)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-SS-8LED2725-12-CS-LSL  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD SILVER, LINEAR SPREAD LENS  
Light Source: (1) SORAA 2700K 90 CRI LED  
SM16-07-25D-927-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 284.8 lumens  
Efficiency: N/A  
Efficacy: 38.5 lumens/watt  
Spacing Criteria (0/90/45): 0.33 / 0.98 / 0.58  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247023  
CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

### Luminous Intensity Polar Plot





TEST NUMBER: P247023

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	85	79	76	91	84	79	75	82	78	75	81	77	74	80	76	74	73
7	89	81	75	72	87	80	75	71	79	74	71	78	74	71	77	73	70	69
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63
10	79	70	65	62	78	70	65	62	69	65	62	69	64	62	68	64	61	60

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	323854	323854	323854
5°	265858	291166	316474
10°	160517	221789	315574
15°	89081	160386	352032
20°	48409	113094	376246
25°	23844	76540	280303
30°	9343	42671	147155
35°	6023	15419	62700
40°	4122	6441	15844
45°	3210	3838	5722
50°	2840	3531	4222
55°	2322	2322	3183
60°	1776	1776	2664
65°	1051	2101	2101
70°	1298	1298	1298
75°	1716	1716	1716
80°	0	0	2557
85°	0	0	0



TEST NUMBER: P247023

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.9	18.2
10°-20°	104.2	36.6
20°-30°	89.8	31.5
30°-40°	28.6	10.0
40°-50°	5.2	1.8
50°-60°	2.8	1.0
60°-70°	1.4	0.5
70°-80°	0.8	0.3
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	245.9	86.3
0°-40°	274.5	96.4
0°-60°	282.5	99.2
0°-90°	284.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	284.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	656	656	656	656	656	
5°	537	557	588	625	639	44
15°	174	212	314	530	689	49
25°	44	61	141	318	515	21
35°	10	12	26	75	104	6
45°	5	5	6	7	8	4
55°	3	3	3	4	4	2
65°	1	1	2	2	2	1
75°	1	1	1	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P247023

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	656.4	656.4	656.4	656.4	656.4
1°	650.0	650.9	650.0	651.8	651.8
2°	631.7	636.3	641.8	650.0	651.8
3°	607.1	615.3	629.0	643.6	648.1
4°	575.1	588.8	610.7	635.4	644.5
5°	536.8	556.9	587.9	625.3	639.0
6°	495.7	519.4	563.3	614.4	634.5
7°	451.9	480.2	535.0	602.5	629.9
8°	408.1	439.1	504.8	587.9	625.3
9°	362.4	398.0	473.8	573.3	627.2
10°	320.4	358.8	442.7	563.3	629.9
11°	282.1	321.3	413.5	553.2	634.5
12°	249.2	289.4	385.2	545.9	643.6
13°	218.2	260.2	360.6	540.4	657.3
14°	194.4	234.6	336.9	535.9	670.1
15°	174.4	211.8	314.0	530.4	689.2
16°	154.3	190.8	293.0	524.9	704.7
17°	136.0	172.5	273.9	517.6	718.4
18°	121.4	154.3	253.8	506.7	723.9
19°	105.0	136.0	234.6	493.9	724.8
20°	92.2	119.6	215.4	476.5	716.6
21°	80.3	105.0	198.1	455.5	696.5
22°	69.4	92.2	184.4	427.2	660.0
23°	59.3	80.3	169.8	396.2	609.8
24°	51.1	70.3	155.2	355.1	566.0
25°	43.8	61.2	140.6	317.7	514.9
26°	36.5	52.0	126.9	283.9	455.5
27°	29.2	43.8	113.2	251.0	391.6
28°	23.7	35.6	99.5	220.0	340.5
29°	19.2	29.2	86.7	191.7	297.6
30°	16.4	23.7	74.9	169.8	258.3
32.5°	12.8	15.5	45.6	119.6	165.2
35°	10.0	11.9	25.6	74.9	104.1
37.5°	7.3	8.2	15.5	37.4	48.4
40°	6.4	7.3	10.0	18.3	24.6
42.5°	5.5	5.5	7.3	10.0	12.8
45°	4.6	4.6	5.5	7.3	8.2
47.5°	3.7	3.7	4.6	5.5	6.4
50°	3.7	3.7	4.6	4.6	5.5
52.5°	2.7	3.7	3.7	3.7	3.7
55°	2.7	2.7	2.7	3.7	3.7
57.5°	2.7	2.7	2.7	2.7	2.7
60°	1.8	1.8	1.8	2.7	2.7
62.5°	0.9	1.8	1.8	1.8	1.8
65°	0.9	0.9	1.8	1.8	1.8



TEST NUMBER: P247023

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
67.5°	0.9	0.9	0.9	0.9	1.8
70°	0.9	0.9	0.9	0.9	0.9
72.5°	0.9	0.9	0.9	0.9	0.9
75°	0.9	0.9	0.9	0.9	0.9
77.5°	0.0	0.9	0.9	0.9	0.9
80°	0.0	0.0	0.0	0.9	0.9
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)