

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P247028

Luminaire Tested: **203-SS-8LED2736-12-BK-LSL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247028  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-33)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-SS-8LED2736-12-BK-LSL  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 36 DEGREE WIDE OPTIC,  
REGRESSED HOOD BLACK, LINEAR SPREAD LENS  
Light Source: (1) SORAA 2700K 95 CRI LED  
SM16-07-36D-927-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 279.0 lumens  
Efficiency: N/A  
Efficacy: 35.8 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.02 / 0.74  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247028  
CATALOG NUMBER: 203-SS-8LED2736-12-BK-LSL

### Luminous Intensity Polar Plot





TEST NUMBER: P247028

CATALOG NUMBER: 203-SS-8LED2736-12-BK-LSL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	87	90	88	86	85
4	100	93	89	85	98	92	88	84	90	86	83	88	85	82	87	84	82	80
5	96	89	83	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76
6	92	84	79	75	90	83	78	75	82	77	74	80	77	74	79	76	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65
9	81	72	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	216199	216199	216199
5°	206624	221532	232378
10°	176098	217230	249243
15°	128718	199563	253655
20°	70933	160086	231964
25°	28798	107353	189827
30°	9343	57711	144079
35°	4397	19816	82456
40°	2383	5861	29369
45°	1256	2582	6349
50°	691	1382	2072
55°	774	774	774
60°	888	888	888
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P247028

CATALOG NUMBER: 203-SS-8LED2736-12-BK-LSL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.1	15.1
10°-20°	104.5	37.5
20°-30°	90.7	32.5
30°-40°	35.9	12.9
40°-50°	4.6	1.7
50°-60°	1.0	0.3
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	237.4	85.1
0°-40°	273.3	98.0
0°-60°	278.9	100.0
0°-90°	279.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	279.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	438	438	438	438	438	
5°	417	429	447	465	469	38
15°	252	296	391	469	497	67
25°	53	78	197	318	349	26
35°	7	10	33	104	137	5
45°	2	3	4	7	9	2
55°	1	1	1	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P247028

CATALOG NUMBER: 203-SS-8LED2736-12-BK-LSL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	438.2	438.2	438.2	438.2	438.2
1°	435.4	436.4	438.2	440.0	440.9
2°	431.8	434.5	439.1	443.7	445.5
3°	428.1	433.6	441.8	450.1	453.7
4°	423.6	431.8	445.5	456.4	461.9
5°	417.2	429.1	447.3	464.7	469.2
6°	409.0	424.5	449.1	469.2	476.5
7°	397.1	418.1	449.1	473.8	483.8
8°	384.3	408.1	444.6	477.4	492.0
9°	368.8	397.1	440.0	480.2	494.8
10°	351.5	383.4	433.6	481.1	497.5
11°	332.3	368.8	428.1	480.2	499.3
12°	314.0	352.4	422.7	479.3	500.3
13°	293.9	335.0	412.6	477.4	500.3
14°	273.9	315.9	401.7	473.8	500.3
15°	252.0	295.8	390.7	469.2	496.6
16°	228.2	274.8	377.9	464.7	490.2
17°	205.4	253.8	363.3	455.5	482.9
18°	180.8	228.2	345.1	442.7	469.2
19°	158.8	203.6	325.9	428.1	455.5
20°	135.1	178.9	304.9	412.6	441.8
21°	113.2	155.2	285.7	395.3	427.2
22°	94.0	130.5	266.6	378.8	409.0
23°	78.5	109.5	242.8	362.4	388.9
24°	64.8	92.2	220.0	342.3	367.9
25°	52.9	77.6	197.2	317.7	348.7
26°	43.8	64.8	176.2	295.8	329.6
27°	34.7	52.9	155.2	273.0	309.5
28°	27.4	42.9	136.0	252.9	289.4
29°	21.9	33.8	117.8	227.3	270.2
30°	16.4	27.4	101.3	207.2	252.9
32.5°	10.0	15.5	61.2	159.8	195.4
35°	7.3	10.0	32.9	104.1	136.9
37.5°	4.6	6.4	16.4	58.4	73.9
40°	3.7	4.6	9.1	27.4	45.6
42.5°	2.7	3.7	5.5	12.8	18.3
45°	1.8	2.7	3.7	7.3	9.1
47.5°	1.8	1.8	1.8	3.7	4.6
50°	0.9	0.9	1.8	1.8	2.7
52.5°	0.9	0.9	0.9	1.8	1.8
55°	0.9	0.9	0.9	0.9	0.9
57.5°	0.9	0.9	0.9	0.9	0.9
60°	0.9	0.9	0.9	0.9	0.9
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P247028

CATALOG NUMBER: 203-SS-8LED2736-12-BK-LSL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)