

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220878

Luminaire Tested: **9004-W1-[RW, RI]-LED5080-F-BK-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220878
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29493)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-[RW, RI]-LED5080-F-BK-L2-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 5000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2013.8 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220878

CATALOG NUMBER: 9004-W1-[RW, RI]-LED5080-F-BK-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220878

CATALOG NUMBER: 9004-W1-[RW, RI]-LED5080-F-BK-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96
2	110	106	103	100	108	105	102	99	101	99	97	99	97	95	96	94	93	91
3	106	101	97	94	104	100	96	93	97	94	92	95	92	90	93	91	89	87
4	102	96	92	88	101	95	91	88	93	90	87	91	88	86	90	87	85	84
5	99	92	87	84	97	91	87	84	89	86	83	88	85	82	86	84	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77
7	92	84	80	76	91	84	79	76	83	79	76	82	78	75	81	77	75	74
8	89	81	76	73	88	81	76	73	80	76	73	79	75	72	78	75	72	71
9	86	78	73	70	85	77	73	70	77	73	70	76	72	70	75	72	69	68
10	83	75	70	67	82	75	70	67	74	70	67	73	70	67	73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	629124
5°	608299
10°	536401
15°	412946
20°	256183
25°	156702
30°	106664
35°	14124
40°	4009
45°	977
50°	768
55°	516
60°	395
65°	467
70°	289
75°	0
80°	0
85°	0



TEST NUMBER: P220878

CATALOG NUMBER: 9004-W1-[RW, RI]-LED5080-F-BK-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	448.8	22.3
10°-20°	867.5	43.1
20°-30°	556.2	27.6
30°-40°	131.1	6.5
40°-50°	6.2	0.3
50°-60°	2.4	0.1
60°-70°	1.3	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1872.5	93.0
0°-40°	2003.6	99.5
0°-60°	2012.2	99.9
0°-90°	2013.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2013.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5100	
5°	4913	449
15°	3234	868
25°	1151	556
35°	94	131
45°	6	6
55°	2	2
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220878

CATALOG NUMBER: 9004-W1-[RW, RI]-LED5080-F-BK-L2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	5100.5
1°	5082.1
2°	5052.4
3°	5018.7
4°	4974.6
5°	4912.9
6°	4830.3
7°	4725.3
8°	4589.0
9°	4440.6
10°	4282.7
11°	4103.8
12°	3912.2
13°	3704.5
14°	3474.4
15°	3233.8
16°	2978.9
17°	2715.0
18°	2452.0
19°	2197.1
20°	1951.7
21°	1733.6
22°	1538.7
23°	1375.2
24°	1250.9
25°	1151.4
26°	1076.9
27°	1019.1
28°	967.8
29°	880.4
30°	748.9
32.5°	357.6
35°	93.8
37.5°	49.7
40°	24.9
42.5°	8.0
45°	5.6
47.5°	4.8
50°	4.0
52.5°	3.2
55°	2.4
57.5°	2.4
60°	1.6
62.5°	1.6
65°	1.6



TEST NUMBER: P220878

CATALOG NUMBER: 9004-W1-[RW, RI]-LED5080-F-BK-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)