

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220980

Luminaire Tested: **9004-W1-FL-LED2790-F-WT-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29495)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED2790-F-WT-L2-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 2700K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1616.0 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220980

CATALOG NUMBER: 9004-W1-FL-LED2790-F-WT-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220980

CATALOG NUMBER: 9004-W1-FL-LED2790-F-WT-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82
5	97	90	85	81	96	89	84	81	87	83	80	86	82	80	84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68
9	83	75	70	67	82	74	70	66	74	69	66	73	69	66	72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63	70	66	63	69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	457181
5°	441766
10°	389260
15°	300573
20°	186588
25°	113804
30°	94387
35°	57611
40°	9758
45°	3559
50°	787
55°	366
60°	296
65°	350
70°	216
75°	286
80°	0
85°	0



TEST NUMBER: P220980

CATALOG NUMBER: 9004-W1-FL-LED2790-F-WT-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	325.9	20.2
10°-20°	630.3	39.0
20°-30°	410.5	25.4
30°-40°	227.9	14.1
40°-50°	17.8	1.1
50°-60°	1.9	0.1
60°-70°	1.1	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1366.7	84.6
0°-40°	1594.6	98.7
0°-60°	1614.3	99.9
0°-90°	1616.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1616.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3706	
5°	3568	326
15°	2354	630
25°	836	410
35°	383	228
45°	20	18
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220980

CATALOG NUMBER: 9004-W1-FL-LED2790-F-WT-L2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	3706.5
1°	3690.2
2°	3666.4
3°	3641.3
4°	3611.6
5°	3567.9
6°	3509.1
7°	3431.7
8°	3335.6
9°	3225.5
10°	3107.9
11°	2979.8
12°	2840.6
13°	2691.5
14°	2527.3
15°	2353.8
16°	2165.1
17°	1968.3
18°	1781.9
19°	1594.4
20°	1421.5
21°	1258.4
22°	1116.9
23°	998.7
24°	906.7
25°	836.2
26°	785.0
27°	744.2
28°	712.2
29°	686.6
30°	662.7
32.5°	561.9
35°	382.6
37.5°	196.2
40°	60.6
42.5°	29.1
45°	20.4
47.5°	12.8
50°	4.1
52.5°	2.3
55°	1.7
57.5°	1.7
60°	1.2
62.5°	1.2
65°	1.2



TEST NUMBER: P220980

CATALOG NUMBER: 9004-W1-FL-LED2790-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.2
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)