

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-42

Luminaire Tested: **203-SS-8LED4025-12-CS-LVR**

Test Date: 04/05/18

Test Information

Test Method: LM-79-08
Report Number: G2-1802-569-42
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-42)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/05/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4025-12-CS-LVR
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD SILVER, HEX CELL LOUVER
Light Source: (1) SORAA 4000K 90 CRI LED
SM16-07-25D-940-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 253.2 lumens
Efficiency: N/A
Efficacy: 35.2 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.3
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): 12.0
Input Current (Ain): 0.629
Voltage Rise (V): NR
Power Factor: 0.9913
Total Harmonic Distortion (THDi): 26.9%
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): 25.2
Test Distance: 25 FT



TEST NUMBER: G2-1802-569-42
CATALOG NUMBER: 203-SS-8LED4025-12-CS-LVR

Luminous Intensity Polar Plot





TEST NUMBER: G2-1802-569-42

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LVR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 115 | 113 | 112 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 102 | 100 | 100 | 99 | 97 |
| 2 | 112 | 109 | 106 | 104 | 110 | 107 | 105 | 103 | 104 | 102 | 100 | 101 | 100 | 98 | 99 | 97 | 96 | 95 |
| 3 | 109 | 105 | 102 | 99 | 107 | 104 | 101 | 98 | 101 | 99 | 97 | 99 | 97 | 95 | 97 | 95 | 94 | 93 |
| 4 | 106 | 101 | 98 | 95 | 105 | 100 | 97 | 95 | 98 | 96 | 94 | 97 | 94 | 92 | 95 | 93 | 91 | 90 |
| 5 | 104 | 98 | 95 | 92 | 102 | 97 | 94 | 92 | 96 | 93 | 91 | 94 | 92 | 90 | 93 | 91 | 89 | 88 |
| 6 | 101 | 96 | 92 | 89 | 100 | 95 | 91 | 89 | 94 | 91 | 88 | 92 | 90 | 88 | 91 | 89 | 87 | 86 |
| 7 | 99 | 93 | 89 | 87 | 98 | 93 | 89 | 87 | 91 | 88 | 86 | 90 | 88 | 86 | 90 | 87 | 85 | 84 |
| 8 | 97 | 91 | 87 | 85 | 96 | 90 | 87 | 85 | 89 | 86 | 84 | 89 | 86 | 84 | 88 | 85 | 84 | 83 |
| 9 | 95 | 89 | 85 | 83 | 94 | 88 | 85 | 83 | 88 | 85 | 82 | 87 | 84 | 82 | 86 | 84 | 82 | 81 |
| 10 | 93 | 87 | 83 | 81 | 92 | 86 | 83 | 81 | 86 | 83 | 81 | 85 | 82 | 81 | 85 | 82 | 80 | 80 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1032150 |
| 5° | 764193 |
| 10° | 389270 |
| 15° | 169580 |
| 20° | 77181 |
| 25° | 28852 |
| 30° | 8546 |
| 35° | 4216 |
| 40° | 2576 |
| 45° | 1395 |
| 50° | 768 |
| 55° | 860 |
| 60° | 0 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: G2-1802-569-42

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LVR

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 121.9 | 48.1 |
| 10°-20° | 97.1 | 38.3 |
| 20°-30° | 27.1 | 10.7 |
| 30°-40° | 5.0 | 2.0 |
| 40°-50° | 1.6 | 0.6 |
| 50°-60° | 0.5 | 0.2 |
| 60°-70° | 0.0 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 246.1 | 97.2 |
| 0°-40° | 251.1 | 99.1 |
| 0°-60° | 253.2 | 100.0 |
| 0°-90° | 253.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 253.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2092 | |
| 5° | 1543 | 122 |
| 15° | 332 | 97 |
| 25° | 53 | 27 |
| 35° | 7 | 5 |
| 45° | 2 | 2 |
| 55° | 1 | 1 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: G2-1802-569-42

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LVR

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|------|
| 0° | 2092 |
| 1° | 2048 |
| 2° | 1958 |
| 3° | 1840 |
| 4° | 1698 |
| 5° | 1543 |
| 6° | 1382 |
| 7° | 1223 |
| 8° | 1067 |
| 9° | 916 |
| 10° | 777 |
| 11° | 650 |
| 12° | 544 |
| 13° | 457 |
| 14° | 387 |
| 15° | 332 |
| 16° | 285 |
| 17° | 244 |
| 18° | 207 |
| 19° | 175 |
| 20° | 147 |
| 22.5° | 90 |
| 25° | 53 |
| 26° | 40 |
| 27° | 32 |
| 28° | 24 |
| 29° | 19 |
| 30° | 15 |
| 32.5° | 11 |
| 35° | 7 |
| 37.5° | 5 |
| 40° | 4 |
| 42.5° | 3 |
| 45° | 2 |
| 47.5° | 1 |
| 50° | 1 |
| 52.5° | 1 |
| 55° | 1 |
| 57.5° | 0 |
| 60° | 0 |
| 62.5° | 0 |
| 65° | 0 |
| 67.5° | 0 |
| 70° | 0 |
| 72.5° | 0 |



TEST NUMBER: G2-1802-569-42

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LVR

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|----|
| 75° | 0 |
| 77.5° | 0 |
| 80° | 0 |
| 82.5° | 0 |
| 85° | 0 |
| 87.5° | 0 |
| 90° | 0 |

(END OF REPORT)