

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P277798

Luminaire Tested: **203-SS-8LED4025-12-CS-LSL**

Test Date: 04/05/18

Test Information

Test Method: LM-79-08
Report Number: P277798
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-41)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/05/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4025-12-CS-LSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD SILVER, LINEAR SPREAD LENS
Light Source: (1) SORAA 4000K 90 CRI LED
SM16-07-25D-940-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 624.1 lumens
Efficiency: N/A
Efficacy: 42.2 lumens/watt
Spacing Criteria (0/90/45): 0.33 / 0.98 / 0.58
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 14.8
Input Voltage (V): 12.0
Input Current (Ain): 0.648
Voltage Rise (V): NR
Power Factor: 0.9912
Total Harmonic Distortion (THDi): 27.0%
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): 25.0
Test Distance: 25 FT



TEST NUMBER: P277798
CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

Luminous Intensity Polar Plot





TEST NUMBER: P277798

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		56	56	56	50
1	100	97	94	92	93	90	88	85	77	75	74		65	64	63		54	53	52	47
2	94	88	84	80	87	82	79	75	71	68	66		61	59	57		51	50	49	45
3	88	81	76	71	82	76	71	67	66	63	60		57	55	53		49	47	46	42
4	83	75	69	64	77	70	65	61	62	58	55		54	51	49		46	45	43	40
5	78	69	63	58	73	65	60	56	58	54	51		51	48	46		44	42	41	38
6	74	64	58	53	69	61	55	51	54	50	47		48	45	43		42	40	39	36
7	69	60	54	49	65	57	51	47	51	47	44		46	43	40		40	38	37	35
8	66	56	50	46	62	53	48	44	48	44	41		43	40	38		39	37	35	33
9	62	53	47	43	59	50	45	41	46	41	39		41	38	36		37	35	33	32
10	59	50	44	40	56	47	42	39	43	39	36		39	36	34		36	33	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	354740	354740	354740
5°	291215	318950	346685
10°	175848	242981	345684
15°	97560	175710	385642
20°	53029	123910	412159
25°	26130	83835	307033
30°	10255	46716	161227
35°	6625	16865	68663
40°	4508	7085	17390
45°	3489	4186	6280
50°	3070	3838	4605
55°	2581	2581	3441
60°	1974	1974	2960
65°	1167	2335	2335
70°	1443	1443	1443
75°	1906	1906	1906
80°	0	0	2841
85°	0	0	0



TEST NUMBER: P277798

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.9	9.1
10°-20°	114.1	18.3
20°-30°	98.4	15.8
30°-40°	31.3	5.0
40°-50°	5.7	0.9
50°-60°	3.1	0.5
60°-70°	1.6	0.2
70°-80°	0.9	0.2
80°-90°	0.1	0.0
90°-100°	0.1	0.0
100°-110°	0.9	0.2
110°-120°	1.6	0.2
120°-130°	3.1	0.5
130°-140°	5.7	0.9
140°-150°	31.3	5.0
150°-160°	98.4	15.8
160°-170°	114.1	18.3
170°-180°	56.9	9.1
0°-30°	269.4	43.2
0°-40°	300.7	48.2
0°-60°	309.5	49.6
0°-90°	312.0	50.0
90°-120°	2.5	0.4
90°-150°	42.6	6.8
90°-180°	312.0	50.0
0°-180°	624.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	719	719	719	719	719	
5°	588	610	644	685	700	48
15°	191	232	344	581	755	54
25°	48	67	154	348	564	22
35°	11	13	28	82	114	7
45°	5	5	6	8	9	4
55°	3	3	3	4	4	3
65°	1	1	2	2	2	1
75°	1	1	1	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	1	1	1	1	1	1
115°	1	1	2	2	2	1
125°	3	3	3	4	4	3
135°	5	5	6	8	9	4
145°	11	13	28	82	114	7
155°	48	67	154	348	564	22
165°	191	232	344	581	755	54
175°	588	610	644	685	700	48
180°	719	719	719	719	719	



TEST NUMBER: P277798

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	719	719	719	719	719
1°	712	713	712	714	714
2°	692	697	703	712	714
3°	665	674	689	705	710
4°	630	645	669	696	706
5°	588	610	644	685	700
6°	543	569	617	673	695
7°	495	526	586	660	690
8°	447	481	553	644	685
9°	397	436	519	628	687
10°	351	393	485	617	690
11°	309	352	453	606	695
12°	273	317	422	598	705
13°	239	285	395	592	720
14°	213	257	369	587	734
15°	191	232	344	581	755
16°	169	209	321	575	772
17°	149	189	300	567	787
18°	133	169	278	555	793
19°	115	149	257	541	794
20°	101	131	236	522	785
21°	88	115	217	499	763
22°	76	101	202	468	723
23°	65	88	186	434	668
24°	56	77	170	389	620
25°	48	67	154	348	564
26°	40	57	139	311	499
27°	32	48	124	275	429
28°	26	39	109	241	373
29°	21	32	95	210	326
30°	18	26	82	186	283
32.5°	14	17	50	131	181
35°	11	13	28	82	114
37.5°	8	9	17	41	53
40°	7	8	11	20	27
42.5°	6	6	8	11	14
45°	5	5	6	8	9
47.5°	4	4	5	6	7
50°	4	4	5	5	6
52.5°	3	4	4	4	4
55°	3	3	3	4	4
57.5°	3	3	3	3	3
60°	2	2	2	3	3
62.5°	1	2	2	2	2
65°	1	1	2	2	2



TEST NUMBER: P277798

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
67.5°	1	1	1	1	2
70°	1	1	1	1	1
72.5°	1	1	1	1	1
75°	1	1	1	1	1
77.5°	0	1	1	1	1
80°	0	0	0	1	1
82.5°	0	0	0	0	0
85°	0	0	0	0	0
87.5°	0	0	0	0	0
90°	0	0	0	0	0
92.5°	0	0	0	0	0
95°	0	0	0	0	0
97.5°	0	0	0	0	0
100°	0	0	0	1	1
102.5°	0	1	1	1	1
105°	1	1	1	1	1
107.5°	1	1	1	1	1
110°	1	1	1	1	1
112.5°	1	1	1	1	2
115°	1	1	2	2	2
117.5°	1	2	2	2	2
120°	2	2	2	3	3
122.5°	3	3	3	3	3
125°	3	3	3	4	4
127.5°	3	4	4	4	4
130°	4	4	5	5	6
132.5°	4	4	5	6	7
135°	5	5	6	8	9
137.5°	6	6	8	11	14
140°	7	8	11	20	27
142.5°	8	9	17	41	53
145°	11	13	28	82	114
147.5°	14	17	50	131	181
150°	18	26	82	186	283
151°	21	32	95	210	326
152°	26	39	109	241	373
153°	32	48	124	275	429
154°	40	57	139	311	499
155°	48	67	154	348	564
156°	56	77	170	389	620
157°	65	88	186	434	668
158°	76	101	202	468	723
159°	88	115	217	499	763
160°	101	131	236	522	785
161°	115	149	257	541	794



TEST NUMBER: P277798

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
162°	133	169	278	555	793
163°	149	189	300	567	787
164°	169	209	321	575	772
165°	191	232	344	581	755
166°	213	257	369	587	734
167°	239	285	395	592	720
168°	273	317	422	598	705
169°	309	352	453	606	695
170°	351	393	485	617	690
171°	397	436	519	628	687
172°	447	481	553	644	685
173°	495	526	586	660	690
174°	543	569	617	673	695
175°	588	610	644	685	700
176°	630	645	669	696	706
177°	665	674	689	705	710
178°	692	697	703	712	714
179°	712	713	712	714	714
180°	719	719	719	719	719

(END OF REPORT)