

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P247010

Luminaire Tested: **203-SS-8LED2710-12-BK-LVR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P247010
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-26)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED2710-12-BK-LVR
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 10 DEGREE SPOT OPTIC, REGRESSED HOOD BLACK, HEX CELL LOUVER
Light Source: (1) SORAA 2700K 95 CRI 10°NSP LED SM16-07-10D-927-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 214.8 lumens
Efficiency: N/A
Efficacy: 26.9 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.19
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247010
CATALOG NUMBER: 203-SS-8LED2710-12-BK-LVR

Luminous Intensity Polar Plot





TEST NUMBER: P247010

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LVR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	116	115	113	112	114	112	111	110	108	108	107	107	105	104	103	103	102	101	101	101	99	99	99	99
2	114	111	109	107	112	109	107	106	106	105	103	103	104	102	101	101	101	100	99	99	98	98	98	98
3	111	108	105	103	110	107	104	103	104	103	101	101	102	101	99	99	100	99	98	98	97	97	97	97
4	109	106	103	101	108	105	102	100	103	101	99	99	101	99	98	98	100	98	97	97	96	96	96	96
5	108	104	101	99	107	103	100	98	101	99	98	98	100	98	97	97	99	97	96	96	95	95	95	95
6	106	102	99	97	105	101	99	97	100	98	96	96	99	97	96	96	98	96	95	95	94	94	94	94
7	105	101	98	96	104	100	97	96	99	97	95	95	98	96	95	95	97	96	94	94	94	94	94	94
8	104	99	97	95	103	99	96	95	98	96	94	94	97	95	94	94	97	95	94	94	93	93	93	93
9	102	98	96	94	102	98	95	94	97	95	93	93	97	95	93	93	96	94	93	93	92	92	92	92
10	101	97	95	93	101	97	94	93	96	94	93	93	96	94	93	93	95	94	92	92	92	92	92	92

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2179011
5°	1419675
10°	151850
15°	43366
20°	18219
25°	8438
30°	5184
35°	3313
40°	1739
45°	1256
50°	691
55°	774
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P247010

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LVR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.9	80.5
10°-20°	28.7	13.4
20°-30°	7.9	3.7
30°-40°	3.6	1.7
40°-50°	1.2	0.6
50°-60°	0.5	0.2
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	209.5	97.5
0°-40°	213.1	99.2
0°-60°	214.8	100.0
0°-90°	214.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	214.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4416	
5°	2866	173
15°	85	29
25°	16	8
35°	6	4
45°	2	1
55°	1	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P247010

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LVR

CANDELA DISTRIBUTION (FULL):

0°	
0°	4416.5
1°	4352.6
2°	4184.7
3°	3888.0
4°	3439.8
5°	2866.5
6°	2196.4
7°	1494.4
8°	904.7
9°	508.5
10°	303.1
12.5°	141.5
15°	84.9
17.5°	56.6
20°	34.7
22.5°	21.9
25°	15.5
27.5°	11.9
30°	9.1
32.5°	7.3
35°	5.5
37.5°	4.6
40°	2.7
42.5°	1.8
45°	1.8
47.5°	0.9
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)