

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P247021

Luminaire Tested: **203-SS-8LED2725-12-CS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P247021
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-8)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED2725-12-CS
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD SILVER
Light Source: (1) SORAA 2700K 90 CRI LED
SM16-07-25D-927-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 330.2 lumens
Efficiency: N/A
Efficacy: 45.2 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.34
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247021
CATALOG NUMBER: 203-SS-8LED2725-12-CS

Luminous Intensity Polar Plot





TEST NUMBER: P247021

CATALOG NUMBER: 203-SS-8LED2725-12-CS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | | | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 111 | 106 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 115 | 113 | 111 | 110 | 113 | 111 | 109 | 108 | 107 | 106 | 105 | 105 | 103 | 102 | 101 | 101 | 100 | 99 | 99 | 99 | 97 | 97 | 97 | 97 |
| 2 | 112 | 108 | 105 | 103 | 110 | 106 | 104 | 102 | 103 | 101 | 99 | 99 | 100 | 99 | 97 | 97 | 98 | 97 | 95 | 95 | 94 | 94 | 94 | 94 |
| 3 | 108 | 104 | 100 | 97 | 106 | 102 | 99 | 97 | 100 | 97 | 95 | 95 | 98 | 96 | 94 | 94 | 96 | 94 | 92 | 92 | 91 | 91 | 91 | 91 |
| 4 | 105 | 100 | 96 | 93 | 104 | 99 | 95 | 93 | 97 | 94 | 92 | 92 | 95 | 93 | 91 | 91 | 93 | 91 | 90 | 90 | 89 | 89 | 89 | 89 |
| 5 | 102 | 97 | 93 | 90 | 101 | 96 | 92 | 89 | 94 | 91 | 89 | 89 | 93 | 90 | 88 | 88 | 91 | 89 | 87 | 87 | 86 | 86 | 86 | 86 |
| 6 | 99 | 94 | 90 | 87 | 98 | 93 | 89 | 86 | 92 | 88 | 86 | 86 | 90 | 88 | 85 | 85 | 89 | 87 | 85 | 85 | 84 | 84 | 84 | 84 |
| 7 | 97 | 91 | 87 | 84 | 96 | 90 | 86 | 84 | 89 | 86 | 83 | 83 | 88 | 85 | 83 | 83 | 87 | 85 | 83 | 83 | 82 | 82 | 82 | 82 |
| 8 | 95 | 88 | 84 | 82 | 94 | 88 | 84 | 82 | 87 | 84 | 81 | 81 | 86 | 83 | 81 | 81 | 85 | 83 | 81 | 81 | 80 | 80 | 80 | 80 |
| 9 | 92 | 86 | 82 | 80 | 91 | 86 | 82 | 79 | 85 | 82 | 79 | 79 | 84 | 81 | 79 | 79 | 83 | 81 | 79 | 79 | 78 | 78 | 78 | 78 |
| 10 | 90 | 84 | 80 | 78 | 89 | 84 | 80 | 78 | 83 | 80 | 77 | 77 | 82 | 79 | 77 | 77 | 82 | 79 | 77 | 77 | 76 | 76 | 76 | 76 |

AVERAGE LUMINANCE (cd/sqm):

| 0° | |
|-----|---------|
| 0° | 1061605 |
| 5° | 849527 |
| 10° | 478396 |
| 15° | 236851 |
| 20° | 116927 |
| 25° | 51172 |
| 30° | 12477 |
| 35° | 6023 |
| 40° | 3542 |
| 45° | 2582 |
| 50° | 2840 |
| 55° | 2322 |
| 60° | 1776 |
| 65° | 1051 |
| 70° | 1298 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P247021

CATALOG NUMBER: 203-SS-8LED2725-12-CS

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 138.3 | 41.9 |
| 10°-20° | 134.0 | 40.6 |
| 20°-30° | 44.1 | 13.4 |
| 30°-40° | 7.0 | 2.1 |
| 40°-50° | 3.2 | 1.0 |
| 50°-60° | 2.4 | 0.7 |
| 60°-70° | 1.0 | 0.3 |
| 70°-80° | 0.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 316.5 | 95.8 |
| 0°-40° | 323.5 | 98.0 |
| 0°-60° | 329.1 | 99.7 |
| 0°-90° | 330.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 330.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2152 | |
| 5° | 1715 | 138 |
| 15° | 464 | 134 |
| 25° | 94 | 44 |
| 35° | 10 | 7 |
| 45° | 4 | 3 |
| 55° | 3 | 2 |
| 65° | 1 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |

TEST NUMBER: P247021

CATALOG NUMBER: 203-SS-8LED2725-12-CS

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 2151.7 |
| 1° | 2121.5 |
| 2° | 2060.4 |
| 3° | 1969.1 |
| 4° | 1852.2 |
| 5° | 1715.3 |
| 6° | 1567.4 |
| 7° | 1411.3 |
| 8° | 1252.5 |
| 9° | 1102.8 |
| 10° | 954.9 |
| 12.5° | 652.7 |
| 15° | 463.7 |
| 17.5° | 328.6 |
| 20° | 222.7 |
| 22.5° | 146.1 |
| 25° | 94.0 |
| 27.5° | 42.9 |
| 30° | 21.9 |
| 32.5° | 14.6 |
| 35° | 10.0 |
| 37.5° | 7.3 |
| 40° | 5.5 |
| 42.5° | 4.6 |
| 45° | 3.7 |
| 47.5° | 3.7 |
| 50° | 3.7 |
| 52.5° | 2.7 |
| 55° | 2.7 |
| 57.5° | 2.7 |
| 60° | 1.8 |
| 62.5° | 0.9 |
| 65° | 0.9 |
| 67.5° | 0.9 |
| 70° | 0.9 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)