

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P221087

Luminaire Tested: **9004-W1-FL-LED3590-F-BK-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221087
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29498)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED3590-F-BK-L2-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3500K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1791.1 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.56
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221087
CATALOG NUMBER: 9004-W1-FL-LED3590-F-BK-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221087

CATALOG NUMBER: 9004-W1-FL-LED3590-F-BK-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	107	104	100	98	100	98	96		97	95	94		95	93	92	90
3	105	99	95	92	103	98	94	91	96	92	90		93	90	88		91	89	87	85
4	101	94	89	86	99	93	89	85	91	87	84		89	86	83		87	85	82	81
5	97	89	84	81	95	88	84	80	87	83	80		85	82	79		84	81	78	77
6	93	85	80	76	91	84	79	76	83	79	75		82	78	75		80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	72		78	74	71		77	74	71	70
8	86	77	72	69	84	77	72	69	76	71	68		75	71	68		74	70	68	67
9	82	74	69	65	81	74	69	65	73	68	65		72	68	65		71	67	65	64
10	79	71	66	63	78	70	66	62	70	65	62		69	65	62		68	65	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	491224
5°	474404
10°	417691
15°	320838
20°	198441
25°	122950
30°	102462
35°	82019
40°	17889
45°	3803
50°	710
55°	409
60°	296
65°	175
70°	216
75°	286
80°	0
85°	0



TEST NUMBER: P221087

CATALOG NUMBER: 9004-W1-FL-LED3590-F-BK-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.9	19.5
10°-20°	673.8	37.6
20°-30°	442.5	24.7
30°-40°	298.4	16.7
40°-50°	23.5	1.3
50°-60°	1.7	0.1
60°-70°	0.8	0.0
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1466.2	81.9
0°-40°	1764.6	98.5
0°-60°	1789.8	99.9
0°-90°	1791.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1791.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3982	
5°	3832	350
15°	2512	674
25°	903	442
35°	545	298
45°	22	24
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P221087

CATALOG NUMBER: 9004-W1-FL-LED3590-F-BK-L2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	3982.5
1°	3965.0
2°	3939.5
3°	3911.4
4°	3878.3
5°	3831.5
6°	3767.3
7°	3683.7
8°	3580.7
9°	3461.5
10°	3334.9
11°	3195.7
12°	3044.1
13°	2878.8
14°	2702.8
15°	2512.5
16°	2312.3
17°	2105.1
18°	1898.0
19°	1703.3
20°	1511.8
21°	1345.8
22°	1196.7
23°	1073.2
24°	977.7
25°	903.4
26°	849.8
27°	808.6
28°	773.7
29°	745.0
30°	719.4
32.5°	665.7
35°	544.7
37.5°	323.8
40°	111.1
42.5°	33.1
45°	21.8
47.5°	13.7
50°	3.7
52.5°	1.9
55°	1.9
57.5°	1.2
60°	1.2
62.5°	1.2
65°	0.6



TEST NUMBER: P221087

CATALOG NUMBER: 9004-W1-FL-LED3590-F-BK-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)