

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220987

Luminaire Tested: **9004-W1-FL-LED3597-F-WT-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220987  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29495)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED3597-F-WT-L2-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 3500K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1714.8 lumens  
Efficiency: N/A  
Efficacy: 85.3 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220987

CATALOG NUMBER: 9004-W1-FL-LED3597-F-WT-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220987

CATALOG NUMBER: 9004-W1-FL-LED3597-F-WT-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82
5	97	90	85	81	96	89	84	81	87	83	80	86	82	80	84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68
9	83	75	70	67	82	74	70	66	74	69	66	73	69	66	72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63	70	66	63	69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	485168
5°	468808
10°	413082
15°	318974
20°	198008
25°	120772
30°	100169
35°	61134
40°	10353
45°	3768
50°	825
55°	409
60°	296
65°	350
70°	216
75°	286
80°	0
85°	0



TEST NUMBER: P220987

CATALOG NUMBER: 9004-W1-FL-LED3597-F-WT-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	345.9	20.2
10°-20°	668.9	39.0
20°-30°	435.6	25.4
30°-40°	241.9	14.1
40°-50°	18.9	1.1
50°-60°	2.0	0.1
60°-70°	1.1	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1450.3	84.6
0°-40°	1692.2	98.7
0°-60°	1713.1	99.9
0°-90°	1714.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1714.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3933	
5°	3786	346
15°	2498	669
25°	887	436
35°	406	242
45°	22	19
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220987

CATALOG NUMBER: 9004-W1-FL-LED3597-F-WT-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3933.4
1°	3916.1
2°	3890.8
3°	3864.2
4°	3832.7
5°	3786.3
6°	3723.9
7°	3641.7
8°	3539.8
9°	3423.0
10°	3298.1
11°	3162.2
12°	3014.5
13°	2856.3
14°	2682.0
15°	2497.9
16°	2297.6
17°	2088.8
18°	1891.0
19°	1692.0
20°	1508.5
21°	1335.4
22°	1185.3
23°	1059.8
24°	962.2
25°	887.4
26°	833.0
27°	789.8
28°	755.8
29°	728.6
30°	703.3
32.5°	596.3
35°	406.0
37.5°	208.3
40°	64.3
42.5°	30.9
45°	21.6
47.5°	13.6
50°	4.3
52.5°	2.5
55°	1.9
57.5°	1.9
60°	1.2
62.5°	1.2
65°	1.2



TEST NUMBER: P220987

CATALOG NUMBER: 9004-W1-FL-LED3597-F-WT-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.2
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)