

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P246989

Luminaire Tested: **203-SS-8LED3036-12-CS-DIFF**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246989
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-44)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED3036-12-CS-DIFF
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 36 DEGREE WIDE OPTIC, REGRESSED HOOD SILVER, DIFFUSED LENS
Light Source: (1) SORAA 3000K 90 CRI LED
SM16-07-36D-930-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 238.2 lumens
Efficiency: N/A
Efficacy: 30.9 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246989
CATALOG NUMBER: 203-SS-8LED3036-12-CS-DIFF

Luminous Intensity Polar Plot





TEST NUMBER: P246989

CATALOG NUMBER: 203-SS-8LED3036-12-CS-DIFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	96	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	79
5	95	87	82	78	93	86	81	78	85	80	77		83	79	76		81	78	76	74
6	91	83	77	73	89	82	77	73	80	76	73		79	75	72		78	74	72	70
7	87	79	73	69	86	78	73	69	77	72	69		76	71	68		74	71	68	67
8	83	75	69	66	82	74	69	65	73	69	65		72	68	65		71	68	65	63
9	80	71	66	62	79	71	66	62	70	65	62		69	65	62		68	64	62	60
10	77	68	63	59	76	68	63	59	67	62	59		66	62	59		66	62	59	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	219554
5°	213360
10°	192330
15°	160744
20°	120077
25°	79643
30°	47969
35°	26140
40°	13719
45°	8024
50°	5450
55°	3785
60°	2664
65°	2101
70°	2597
75°	1716
80°	2557
85°	0



TEST NUMBER: P246989

CATALOG NUMBER: 203-SS-8LED3036-12-CS-DIFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	16.6
10°-20°	86.0	36.1
20°-30°	67.1	28.2
30°-40°	28.7	12.0
40°-50°	9.5	4.0
50°-60°	4.0	1.7
60°-70°	2.1	0.9
70°-80°	1.1	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	192.7	80.9
0°-40°	221.4	92.9
0°-60°	234.9	98.6
0°-90°	238.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	238.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	445	
5°	431	40
15°	315	86
25°	146	67
35°	43	29
45°	12	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P246989

CATALOG NUMBER: 203-SS-8LED3036-12-CS-DIFF

CANDELA DISTRIBUTION (FULL):

0°	
0°	445.0
1°	442.4
2°	440.6
3°	437.9
4°	435.3
5°	430.8
6°	424.6
7°	416.7
8°	407.8
9°	396.3
10°	383.9
11°	370.6
12°	358.1
13°	344.0
14°	329.8
15°	314.7
16°	298.7
17°	281.9
18°	264.2
19°	247.3
20°	228.7
21°	210.1
22°	192.4
23°	176.4
24°	160.5
25°	146.3
26°	132.1
27°	118.8
28°	106.4
29°	94.9
30°	84.2
32.5°	60.3
35°	43.4
37.5°	31.0
40°	21.3
42.5°	15.1
45°	11.5
47.5°	8.9
50°	7.1
52.5°	5.3
55°	4.4
57.5°	3.5
60°	2.7
62.5°	2.7
65°	1.8



TEST NUMBER: P246989
CATALOG NUMBER: 203-SS-8LED3036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.8
70°	1.8
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)