

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220983

Luminaire Tested: **9004-W1-FL-LED4080-F-WT-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220983  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29495)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED4080-F-WT-L2-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 4000K CCT, 80 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2141.9 lumens  
Efficiency: N/A  
Efficacy: 106.6 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220983

CATALOG NUMBER: 9004-W1-FL-LED4080-F-WT-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220983

CATALOG NUMBER: 9004-W1-FL-LED4080-F-WT-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	96	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	67	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	605997
5°	585567
10°	515961
15°	398401
20°	247310
25°	150850
30°	125108
35°	76358
40°	12930
45°	4710
50°	1036
55°	495
60°	370
65°	438
70°	289
75°	381
80°	0
85°	0



TEST NUMBER: P220983

CATALOG NUMBER: 9004-W1-FL-LED4080-F-WT-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	432.0	20.2
10°-20°	835.4	39.0
20°-30°	544.1	25.4
30°-40°	302.2	14.1
40°-50°	23.6	1.1
50°-60°	2.5	0.1
60°-70°	1.4	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1811.5	84.6
0°-40°	2113.6	98.7
0°-60°	2139.7	99.9
0°-90°	2141.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2141.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4913	
5°	4729	432
15°	3120	835
25°	1108	544
35°	507	302
45°	27	24
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220983

CATALOG NUMBER: 9004-W1-FL-LED4080-F-WT-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4913.0
1°	4891.4
2°	4859.7
3°	4826.5
4°	4787.2
5°	4729.3
6°	4651.3
7°	4548.7
8°	4421.3
9°	4275.4
10°	4119.5
11°	3949.7
12°	3765.2
13°	3567.6
14°	3349.9
15°	3119.9
16°	2869.8
17°	2608.9
18°	2361.9
19°	2113.4
20°	1884.1
21°	1668.0
22°	1480.5
23°	1323.8
24°	1201.8
25°	1108.4
26°	1040.5
27°	986.5
28°	944.0
29°	910.0
30°	878.4
32.5°	744.9
35°	507.1
37.5°	260.1
40°	80.3
42.5°	38.6
45°	27.0
47.5°	17.0
50°	5.4
52.5°	3.1
55°	2.3
57.5°	2.3
60°	1.5
62.5°	1.5
65°	1.5



TEST NUMBER: P220983

CATALOG NUMBER: 9004-W1-FL-LED4080-F-WT-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.5
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)