

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220934

Luminaire Tested: **9004-W1-FL-LED4097-S-WT-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220934  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29496)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED4097-S-WT-L2-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, SPOT OPTIC,  
WHITE HOUSING.  
Light Source: (1) 4000K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1714.4 lumens  
Efficiency: N/A  
Efficacy: 85.3 lumens/watt  
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220934

CATALOG NUMBER: 9004-W1-FL-LED4097-S-WT-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220934

CATALOG NUMBER: 9004-W1-FL-LED4097-S-WT-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	104	103	101	100	99	98	98	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81
6	95	89	84	81	94	88	83	80	86	83	80	85	82	79	84	81	79	78
7	92	85	80	77	91	85	80	77	83	79	77	82	79	76	81	78	76	75
8	89	82	77	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72
9	87	79	75	72	86	79	74	71	78	74	71	77	74	71	76	73	71	70
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1327865
5°	1033610
10°	430491
15°	182019
20°	124922
25°	99705
30°	92136
35°	75379
40°	15860
45°	3628
50°	1286
55°	1054
60°	592
65°	350
70°	216
75°	286
80°	0
85°	0



TEST NUMBER: P220934

CATALOG NUMBER: 9004-W1-FL-LED4097-S-WT-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	627.4	36.6
10°-20°	439.7	25.6
20°-30°	346.5	20.2
30°-40°	272.8	15.9
40°-50°	22.0	1.3
50°-60°	4.3	0.2
60°-70°	1.1	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1413.6	82.5
0°-40°	1686.4	98.4
0°-60°	1712.7	99.9
0°-90°	1714.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1714.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10765	
5°	8348	627
15°	1425	440
25°	733	347
35°	501	273
45°	21	22
55°	5	4
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220934

CATALOG NUMBER: 9004-W1-FL-LED4097-S-WT-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10765.4
1°	10617.3
2°	10309.5
3°	9832.1
4°	9179.1
5°	8347.9
6°	7388.3
7°	6351.5
8°	5334.4
9°	4310.5
10°	3437.1
11°	2740.0
12°	2234.5
13°	1876.5
14°	1617.0
15°	1425.4
16°	1281.6
17°	1176.3
18°	1096.1
19°	1019.6
20°	951.7
21°	895.4
22°	845.2
23°	801.1
24°	762.6
25°	732.6
26°	709.9
27°	692.8
28°	676.3
29°	661.6
30°	646.9
32.5°	610.2
35°	500.6
37.5°	298.7
40°	98.5
42.5°	29.4
45°	20.8
47.5°	14.7
50°	6.7
52.5°	6.1
55°	4.9
57.5°	3.7
60°	2.4
62.5°	1.2
65°	1.2



TEST NUMBER: P220934

CATALOG NUMBER: 9004-W1-FL-LED4097-S-WT-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)