

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220957

Luminaire Tested: **9004-W1-FL-LED5080-M-WT-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29497)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED5080-M-WT-L2-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 5000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2266.2 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220957

CATALOG NUMBER: 9004-W1-FL-LED5080-M-WT-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220957

CATALOG NUMBER: 9004-W1-FL-LED5080-M-WT-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86
4	101	95	91	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82
5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78
6	94	86	82	78	92	86	81	78	84	80	77	83	79	77	82	79	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	914571
5°	839230
10°	616636
15°	358994
20°	195764
25°	139145
30°	125393
35°	98764
40°	21947
45°	6018
50°	1996
55°	1204
60°	789
65°	467
70°	289
75°	381
80°	0
85°	0



TEST NUMBER: P220957

CATALOG NUMBER: 9004-W1-FL-LED5080-M-WT-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	587.2	25.9
10°-20°	783.6	34.6
20°-30°	490.1	21.6
30°-40°	363.5	16.0
40°-50°	33.9	1.5
50°-60°	5.4	0.2
60°-70°	1.9	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1860.8	82.1
0°-40°	2224.3	98.2
0°-60°	2263.6	99.9
0°-90°	2266.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2266.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7415	
5°	6778	587
15°	2811	784
25°	1022	490
35°	656	363
45°	34	34
55°	6	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220957

CATALOG NUMBER: 9004-W1-FL-LED5080-M-WT-L2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	7414.7
1°	7365.8
2°	7282.4
3°	7162.1
4°	6996.9
5°	6778.0
6°	6506.2
7°	6178.2
8°	5795.7
9°	5369.2
10°	4923.3
11°	4467.1
12°	4025.3
13°	3594.7
14°	3185.7
15°	2811.3
16°	2470.5
17°	2173.0
18°	1906.0
19°	1679.9
20°	1491.4
21°	1342.3
22°	1222.8
23°	1134.6
24°	1069.7
25°	1022.4
26°	987.1
27°	956.6
28°	928.5
29°	904.5
30°	880.4
32.5°	813.9
35°	655.9
37.5°	396.9
40°	136.3
42.5°	47.3
45°	34.5
47.5°	24.9
50°	10.4
52.5°	8.0
55°	5.6
57.5°	4.0
60°	3.2
62.5°	2.4
65°	1.6



TEST NUMBER: P220957

CATALOG NUMBER: 9004-W1-FL-LED5080-M-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.6
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)