

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220862

Luminaire Tested: **9004-W1-[RW, RI]-LED3097-M-BK-L3-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220862  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29492)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-[RW, RI]-LED3097-M-BK-L3-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 3000K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1746.8 lumens  
Efficiency: N/A  
Efficacy: 61.3 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 28.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220862

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L3-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220862

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L3-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79
7	93	86	82	79	92	86	81	78	85	81	78	84	80	78	83	80	77	76
8	90	83	79	76	89	83	78	76	82	78	75	81	77	75	80	77	75	74
9	88	80	76	73	87	80	76	73	79	75	73	78	75	72	78	75	72	71
10	85	78	73	70	84	77	73	70	77	73	70	76	73	70	75	72	70	69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	802536
5°	736301
10°	543253
15°	317084
20°	171953
25°	121521
30°	88063
35°	10947
40°	3752
45°	1483
50°	940
55°	753
60°	518
65°	409
70°	252
75°	334
80°	497
85°	0



TEST NUMBER: P220862

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L3-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	515.6	29.5
10°-20°	691.5	39.6
20°-30°	419.5	24.0
30°-40°	107.3	6.1
40°-50°	7.7	0.4
50°-60°	3.1	0.2
60°-70°	1.4	0.1
70°-80°	0.7	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1626.5	93.1
0°-40°	1733.8	99.3
0°-60°	1744.6	99.9
0°-90°	1746.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1746.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6506	
5°	5947	516
15°	2483	691
25°	893	419
35°	73	107
45°	8	8
55°	4	3
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220862

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L3-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6506.4
1°	6464.8
2°	6390.7
3°	6284.8
4°	6140.1
5°	5946.7
6°	5705.3
7°	5433.5
8°	5086.3
9°	4715.7
10°	4337.4
11°	3939.3
12°	3548.3
13°	3174.2
14°	2814.9
15°	2483.1
16°	2186.7
17°	1919.2
18°	1680.6
19°	1479.4
20°	1310.0
21°	1176.6
22°	1070.8
23°	992.4
24°	936.6
25°	892.9
26°	857.6
27°	827.2
28°	791.2
29°	725.6
30°	618.3
32.5°	294.3
35°	72.7
37.5°	39.5
40°	23.3
42.5°	10.6
45°	8.5
47.5°	7.1
50°	4.9
52.5°	4.2
55°	3.5
57.5°	2.8
60°	2.1
62.5°	2.1
65°	1.4



TEST NUMBER: P220862

CATALOG NUMBER: 9004-W1-[RW, RI]-LED3097-M-BK-L3-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)