

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220962

Luminaire Tested: **9004-W1-FL-LED2790-M-WT-L3-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220962  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29497)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED2790-M-WT-L3-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 2700K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2132.2 lumens  
Efficiency: N/A  
Efficacy: 74.6 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 28.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220962

CATALOG NUMBER: 9004-W1-FL-LED2790-M-WT-L3-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220962

CATALOG NUMBER: 9004-W1-FL-LED2790-M-WT-L3-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86
4	101	95	91	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82
5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78
6	94	86	82	78	92	86	81	78	84	80	77	83	79	77	82	79	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	860496
5°	789617
10°	580176
15°	337771
20°	184200
25°	130912
30°	117987
35°	92921
40°	20658
45°	5652
50°	1881
55°	1140
60°	740
65°	438
70°	289
75°	381
80°	0
85°	0



TEST NUMBER: P220962

CATALOG NUMBER: 9004-W1-FL-LED2790-M-WT-L3-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	552.4	25.9
10°-20°	737.3	34.6
20°-30°	461.1	21.6
30°-40°	342.0	16.0
40°-50°	31.9	1.5
50°-60°	5.1	0.2
60°-70°	1.8	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1750.8	82.1
0°-40°	2092.8	98.1
0°-60°	2129.7	99.9
0°-90°	2132.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2132.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6976	
5°	6377	552
15°	2645	737
25°	962	461
35°	617	342
45°	32	32
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220962

CATALOG NUMBER: 9004-W1-FL-LED2790-M-WT-L3-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6976.3
1°	6930.3
2°	6851.8
3°	6738.6
4°	6583.2
5°	6377.3
6°	6121.5
7°	5812.9
8°	5453.1
9°	5051.7
10°	4632.2
11°	4203.0
12°	3787.3
13°	3382.1
14°	2997.4
15°	2645.1
16°	2324.4
17°	2044.5
18°	1793.3
19°	1580.5
20°	1403.3
21°	1262.9
22°	1150.5
23°	1067.5
24°	1006.4
25°	961.9
26°	928.7
27°	900.0
28°	873.6
29°	851.0
30°	828.4
32.5°	765.8
35°	617.1
37.5°	373.4
40°	128.3
42.5°	44.5
45°	32.4
47.5°	23.4
50°	9.8
52.5°	7.5
55°	5.3
57.5°	3.8
60°	3.0
62.5°	2.3
65°	1.5



TEST NUMBER: P220962

CATALOG NUMBER: 9004-W1-FL-LED2790-M-WT-L3-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.5
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)