

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P221124

Luminaire Tested: **9004-W1-FL-LED2797-W-BK-L3-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P221124  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29499)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED2797-W-BK-L3-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, WIDE FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 2700K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1951.0 lumens  
Efficiency: N/A  
Efficacy: 68.5 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.91  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 28.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P221124

CATALOG NUMBER: 9004-W1-FL-LED2797-W-BK-L3-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P221124

CATALOG NUMBER: 9004-W1-FL-LED2797-W-BK-L3-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78	74	72	70
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74	70	67	65
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70	66	63	61
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66	62	59	57
9	75	66	60	56	74	65	60	56	64	59	56		63	59	55		63	58	55	54
10	72	62	56	53	71	62	56	52	61	56	52		60	55	52		59	55	52	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	273667
5°	278786
10°	269923
15°	248587
20°	213038
25°	181676
30°	155360
35°	116140
40°	41204
45°	19275
50°	12742
55°	8580
60°	4317
65°	1022
70°	757
75°	667
80°	0
85°	0



TEST NUMBER: P221124

CATALOG NUMBER: 9004-W1-FL-LED2797-W-BK-L3-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	211.9	10.9
10°-20°	537.3	27.5
20°-30°	613.3	31.4
30°-40°	450.3	23.1
40°-50°	95.6	4.9
50°-60°	36.1	1.9
60°-70°	5.1	0.3
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1362.5	69.8
0°-40°	1812.8	92.9
0°-60°	1944.5	99.7
0°-90°	1951.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1951.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2219	
5°	2252	212
15°	1947	537
25°	1335	613
35°	771	450
45°	110	96
55°	40	36
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P221124

CATALOG NUMBER: 9004-W1-FL-LED2797-W-BK-L3-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2218.7
1°	2218.0
2°	2223.6
3°	2234.8
4°	2245.3
5°	2251.6
6°	2250.2
7°	2238.3
8°	2215.2
9°	2186.5
10°	2155.1
11°	2119.4
12°	2083.1
13°	2041.8
14°	1997.0
15°	1946.7
16°	1889.4
17°	1825.7
18°	1760.0
19°	1690.8
20°	1623.0
21°	1560.0
22°	1499.2
23°	1441.8
24°	1387.3
25°	1334.9
26°	1283.8
27°	1232.1
28°	1182.4
29°	1136.3
30°	1090.8
32.5°	968.5
35°	771.3
37.5°	520.9
40°	255.9
42.5°	144.0
45°	110.5
47.5°	86.7
50°	66.4
52.5°	52.4
55°	39.9
57.5°	28.7
60°	17.5
62.5°	4.9
65°	3.5



TEST NUMBER: P221124

CATALOG NUMBER: 9004-W1-FL-LED2797-W-BK-L3-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	2.8
70°	2.1
72.5°	2.1
75°	1.4
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)