

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220965

Luminaire Tested: **9004-W1-FL-LED4080-M-WT-L3-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29497)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W1-FL-LED4080-M-WT-L3-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2826.2 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 28.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220965

CATALOG NUMBER: 9004-W1-FL-LED4080-M-WT-L3-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220965

CATALOG NUMBER: 9004-W1-FL-LED4080-M-WT-L3-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86
4	101	95	91	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82
5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78
6	94	86	82	78	92	86	81	78	84	80	77	83	79	77	82	79	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1140577
5°	1046623
10°	769025
15°	447705
20°	244147
25°	173523
30°	156385
35°	123172
40°	27373
45°	7501
50°	2495
55°	1505
60°	987
65°	584
70°	361
75°	477
80°	0
85°	0



TEST NUMBER: P220965

CATALOG NUMBER: 9004-W1-FL-LED4080-M-WT-L3-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	732.3	25.9
10°-20°	977.2	34.6
20°-30°	611.2	21.6
30°-40°	453.3	16.0
40°-50°	42.2	1.5
50°-60°	6.8	0.2
60°-70°	2.3	0.1
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2320.7	82.1
0°-40°	2774.0	98.2
0°-60°	2822.9	99.9
0°-90°	2826.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2826.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9247	
5°	8453	732
15°	3506	977
25°	1275	611
35°	818	453
45°	43	42
55°	7	7
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220965

CATALOG NUMBER: 9004-W1-FL-LED4080-M-WT-L3-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	9247
1°	9186
2°	9082
3°	8932
4°	8726
5°	8453
6°	8114
7°	7705
8°	7228
9°	6696
10°	6140
11°	5571
12°	5020
13°	4483
14°	3973
15°	3506
16°	3081
17°	2710
18°	2377
19°	2095
20°	1860
21°	1674
22°	1525
23°	1415
24°	1334
25°	1275
26°	1231
27°	1193
28°	1158
29°	1128
30°	1098
32.5°	1015
35°	818
37.5°	495
40°	170
42.5°	59
45°	43
47.5°	31
50°	13
52.5°	10
55°	7
57.5°	5
60°	4
62.5°	3
65°	2



TEST NUMBER: P220965

CATALOG NUMBER: 9004-W1-FL-LED4080-M-WT-L3-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	2
70°	1
72.5°	1
75°	1
77.5°	1
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)