

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220970

Luminaire Tested: **9004-W1-FL-LED4097-M-WT-L3-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220970  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29497)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9004-W1-FL-LED4097-M-WT-L3-UNV  
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 4000K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2241.0 lumens  
Efficiency: N/A  
Efficacy: 78.4 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct


Input Watts (W): 28.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220970

CATALOG NUMBER: 9004-W1-FL-LED4097-M-WT-L3-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220970

CATALOG NUMBER: 9004-W1-FL-LED4097-M-WT-L3-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86
4	101	95	91	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82
5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78
6	94	86	82	78	92	86	81	78	84	80	77	83	79	77	82	79	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	904370
5°	829870
10°	609759
15°	354984
20°	193585
25°	137594
30°	123997
35°	97664
40°	21705
45°	5948
50°	1976
55°	1204
60°	789
65°	467
70°	289
75°	381
80°	0
85°	0



TEST NUMBER: P220970

CATALOG NUMBER: 9004-W1-FL-LED4097-M-WT-L3-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	580.6	25.9
10°-20°	774.9	34.6
20°-30°	484.6	21.6
30°-40°	359.4	16.0
40°-50°	33.5	1.5
50°-60°	5.4	0.2
60°-70°	1.9	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1840.1	82.1
0°-40°	2199.5	98.1
0°-60°	2238.4	99.9
0°-90°	2241.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2241.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7332	
5°	6702	581
15°	2780	775
25°	1011	485
35°	649	359
45°	34	33
55°	6	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220970

CATALOG NUMBER: 9004-W1-FL-LED4097-M-WT-L3-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7332.0
1°	7283.6
2°	7201.1
3°	7082.2
4°	6918.9
5°	6702.4
6°	6433.6
7°	6109.3
8°	5731.1
9°	5309.3
10°	4868.4
11°	4417.3
12°	3980.4
13°	3554.6
14°	3150.2
15°	2779.9
16°	2442.9
17°	2148.8
18°	1884.7
19°	1661.1
20°	1474.8
21°	1327.3
22°	1209.2
23°	1122.0
24°	1057.7
25°	1011.0
26°	976.1
27°	945.9
28°	918.2
29°	894.4
30°	870.6
32.5°	804.8
35°	648.6
37.5°	392.5
40°	134.8
42.5°	46.8
45°	34.1
47.5°	24.6
50°	10.3
52.5°	7.9
55°	5.6
57.5°	4.0
60°	3.2
62.5°	2.4
65°	1.6



TEST NUMBER: P220970

CATALOG NUMBER: 9004-W1-FL-LED4097-M-WT-L3-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.6
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)