

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P221787

Luminaire Tested: **9004-W2-[RW, RI]-LED3090-W-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221787
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29494)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W2-[RW, RI]-LED3090-W-BK-L1-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, WIDE FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1592.6 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 19.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221787

CATALOG NUMBER: 9004-W2-[RW, RI]-LED3090-W-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221787

CATALOG NUMBER: 9004-W2-[RW, RI]-LED3090-W-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	100	97	94	91	93	90	87	85	77	75	74	65	64	63	53	53	52	47
2	94	88	83	79	87	82	78	75	71	68	66	60	59	57	51	50	49	44
3	88	80	75	70	81	75	70	67	65	62	59	56	54	52	48	47	45	42
4	82	74	68	63	76	69	64	60	61	57	54	53	50	48	46	44	42	39
5	77	68	62	57	72	64	58	54	57	52	49	50	47	44	43	41	40	37
6	72	63	56	52	68	59	54	50	53	49	45	47	44	41	41	39	37	35
7	68	58	52	47	64	55	50	46	49	45	42	44	41	38	39	37	35	33
8	64	54	48	44	60	52	46	42	46	42	39	41	38	36	37	35	33	31
9	61	51	45	40	57	48	43	39	44	39	36	39	36	34	35	33	31	29
10	58	48	42	38	54	45	40	36	41	37	34	37	34	32	33	31	29	28

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132091
5°	134255
10°	129407
15°	118950
20°	101557
25°	85319
30°	63864
35°	20042
40°	11867
45°	7222
50°	3013
55°	495
60°	321
65°	204
70°	108
75°	143
80°	0
85°	0



TEST NUMBER: P221787

CATALOG NUMBER: 9004-W2-[RW, RI]-LED3090-W-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.9	6.4
10°-20°	256.9	16.1
20°-30°	286.1	18.0
30°-40°	114.2	7.2
40°-50°	32.6	2.0
50°-60°	3.6	0.2
60°-70°	0.7	0.0
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.3	0.0
110°-120°	0.7	0.0
120°-130°	3.6	0.2
130°-140°	32.6	2.0
140°-150°	114.2	7.2
150°-160°	286.1	18.0
160°-170°	256.9	16.1
170°-180°	101.9	6.4
0°-30°	644.9	40.5
0°-40°	759.1	47.7
0°-60°	795.3	49.9
0°-90°	796.3	50.0
90°-120°	1.0	0.1
90°-150°	151.4	9.5
90°-180°	796.0	50.0
0°-180°	1592.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1071	
5°	1084	102
15°	932	257
25°	627	286
35°	133	114
45°	41	33
55°	2	4
65°	1	1
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	1	1
125°	2	4
135°	41	33
145°	133	114
155°	627	286
165°	932	257
175°	1084	102
180°	1071	



TEST NUMBER: P221787

CATALOG NUMBER: 9004-W2-[RW, RI]-LED3090-W-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	1070.9
1°	1070.6
2°	1072.6
3°	1077.6
4°	1082.3
5°	1084.3
6°	1082.9
7°	1075.9
8°	1063.9
9°	1049.2
10°	1033.2
11°	1015.9
12°	997.9
13°	977.8
14°	955.8
15°	931.5
16°	903.1
17°	872.8
18°	839.7
19°	806.0
20°	773.7
21°	742.3
22°	712.3
23°	682.9
24°	655.2
25°	626.9
26°	600.2
27°	577.2
28°	553.1
29°	510.8
30°	448.4
32.5°	262.2
35°	133.1
37.5°	98.4
40°	73.7
42.5°	54.7
45°	41.4
47.5°	30.7
50°	15.7
52.5°	4.0
55°	2.3
57.5°	1.7
60°	1.3
62.5°	1.0
65°	0.7



TEST NUMBER: P221787

CATALOG NUMBER: 9004-W2-[RW, RI]-LED3090-W-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.3
105°	0.3
107.5°	0.3
110°	0.3
112.5°	0.3
115°	0.7
117.5°	1.0
120°	1.3
122.5°	1.7
125°	2.3
127.5°	4.0
130°	15.7
132.5°	30.7
135°	41.4
137.5°	54.7
140°	73.7
142.5°	98.4
145°	133.1
147.5°	262.2
150°	448.4
151°	510.8
152°	553.1
153°	577.2
154°	600.2
155°	626.9
156°	655.2
157°	682.9
158°	712.3
159°	742.3
160°	773.7
161°	806.0



TEST NUMBER: P221787

CATALOG NUMBER: 9004-W2-[RW, RI]-LED3090-W-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
162°	839.7
163°	872.8
164°	903.1
165°	931.5
166°	955.8
167°	977.8
168°	997.9
169°	1015.9
170°	1033.2
171°	1049.2
172°	1063.9
173°	1075.9
174°	1082.9
175°	1084.3
176°	1082.3
177°	1077.6
178°	1072.6
179°	1070.6
180°	1070.9

(END OF REPORT)