

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P222060

Luminaire Tested: **9004-W2-FL-LED3590-F-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P222060
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29495)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W2-FL-LED3590-F-WT-L1-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, FLUSH LENS, FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 3500K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1875.3 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 19.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222060

CATALOG NUMBER: 9004-W2-FL-LED3590-F-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P222060

CATALOG NUMBER: 9004-W2-FL-LED3590-F-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		56	56	56	50
1	100	97	94	92	93	90	88	86	77	75	74		65	64	63		54	53	53	48
2	94	89	84	80	87	83	79	76	71	69	67		61	59	58		51	50	50	45
3	88	81	76	72	82	76	72	68	67	63	61		58	55	53		49	48	47	43
4	83	75	69	65	77	71	66	62	62	58	56		54	52	50		47	45	44	41
5	78	70	63	59	73	66	60	56	58	54	51		51	49	46		45	43	42	39
6	74	65	59	54	69	61	56	52	55	51	48		49	46	44		43	41	40	37
7	70	61	54	50	66	57	52	48	52	48	45		46	43	41		41	39	38	35
8	66	57	51	47	62	54	49	45	49	45	42		44	41	39		39	37	36	34
9	63	53	47	44	59	51	46	42	46	42	39		42	39	37		38	36	34	32
10	60	50	45	41	57	48	43	40	44	40	37		40	37	35		36	34	33	31

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	265292
5°	256350
10°	225873
15°	174408
20°	108265
25°	66034
30°	54763
35°	33428
40°	5652
45°	2058
50°	461
55°	215
60°	173
65°	204
70°	108
75°	143
80°	0
85°	0



TEST NUMBER: P222060

CATALOG NUMBER: 9004-W2-FL-LED3590-F-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.1	10.1
10°-20°	365.7	19.5
20°-30°	238.2	12.7
30°-40°	132.3	7.1
40°-50°	10.3	0.6
50°-60°	1.1	0.1
60°-70°	0.6	0.0
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.3	0.0
110°-120°	0.6	0.0
120°-130°	1.1	0.1
130°-140°	10.3	0.6
140°-150°	132.3	7.1
150°-160°	238.2	12.7
160°-170°	365.7	19.5
170°-180°	189.1	10.1
0°-30°	793.0	42.3
0°-40°	925.3	49.3
0°-60°	936.7	50.0
0°-90°	937.7	50.0
90°-120°	0.9	0.0
90°-150°	144.6	7.7
90°-180°	938.0	50.0
0°-180°	1875.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2151	
5°	2070	189
15°	1366	366
25°	485	238
35°	222	132
45°	12	10
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	1	1
125°	1	1
135°	12	10
145°	222	132
155°	485	238
165°	1366	366
175°	2070	189
180°	2151	



TEST NUMBER: P222060

CATALOG NUMBER: 9004-W2-FL-LED3590-F-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2150.8
1°	2141.4
2°	2127.5
3°	2113.0
4°	2095.7
5°	2070.4
6°	2036.3
7°	1991.3
8°	1935.6
9°	1871.7
10°	1803.4
11°	1729.1
12°	1648.3
13°	1561.8
14°	1466.5
15°	1365.8
16°	1256.4
17°	1142.1
18°	1034.0
19°	925.2
20°	824.8
21°	730.2
22°	648.1
23°	579.5
24°	526.1
25°	485.2
26°	455.5
27°	431.9
28°	413.3
29°	398.4
30°	384.5
32.5°	326.1
35°	222.0
37.5°	113.9
40°	35.1
42.5°	16.9
45°	11.8
47.5°	7.4
50°	2.4
52.5°	1.4
55°	1.0
57.5°	1.0
60°	0.7
62.5°	0.7
65°	0.7



TEST NUMBER: P222060

CATALOG NUMBER: 9004-W2-FL-LED3590-F-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.3
105°	0.3
107.5°	0.3
110°	0.3
112.5°	0.7
115°	0.7
117.5°	0.7
120°	0.7
122.5°	1.0
125°	1.0
127.5°	1.4
130°	2.4
132.5°	7.4
135°	11.8
137.5°	16.9
140°	35.1
142.5°	113.9
145°	222.0
147.5°	326.1
150°	384.5
151°	398.4
152°	413.3
153°	431.9
154°	455.5
155°	485.2
156°	526.1
157°	579.5
158°	648.1
159°	730.2
160°	824.8
161°	925.2



TEST NUMBER: P222060

CATALOG NUMBER: 9004-W2-FL-LED3590-F-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
162°	1034.0
163°	1142.1
164°	1256.4
165°	1365.8
166°	1466.5
167°	1561.8
168°	1648.3
169°	1729.1
170°	1803.4
171°	1871.7
172°	1935.6
173°	1991.3
174°	2036.3
175°	2070.4
176°	2095.7
177°	2113.0
178°	2127.5
179°	2141.4
180°	2150.8

(END OF REPORT)