

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P221785

Luminaire Tested: **9004-W2-[RW, RI]-LED3090-S-WT-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221785
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29487)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9004-W2-[RW, RI]-LED3090-S-WT-L2-UNV
Description: LUMIERE LANTERRA 9004 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC, WHITE HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3254.2 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221785

CATALOG NUMBER: 9004-W2-[RW, RI]-LED3090-S-WT-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221785

CATALOG NUMBER: 9004-W2-[RW, RI]-LED3090-S-WT-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		56	56	56	50
1	100	97	94	92	93	90	88	86	77	75	74		65	64	63		54	53	53	48
2	94	89	85	81	87	83	79	76	72	69	67		61	60	58		52	51	50	46
3	89	82	77	72	83	77	72	69	67	64	61		58	56	54		50	48	47	44
4	84	76	70	66	78	72	67	63	63	60	57		55	53	51		48	46	45	42
5	79	71	65	61	74	67	62	58	60	56	53		53	50	48		46	45	43	41
6	75	67	61	56	71	63	58	54	57	53	50		50	48	46		45	43	42	39
7	72	63	57	53	67	60	54	51	54	50	47		48	46	44		43	42	40	38
8	68	59	54	50	65	57	52	48	51	48	45		47	44	42		42	40	39	37
9	66	56	51	47	62	54	49	46	49	46	43		45	42	40		41	39	38	36
10	63	54	48	45	59	52	47	43	47	44	41		43	41	39		40	38	36	35

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1344874
5°	1045076
10°	442866
15°	189336
20°	129293
25°	103039
30°	77039
35°	10209
40°	5458
45°	3977
50°	4260
55°	4645
60°	5156
65°	5925
70°	6888
75°	8197
80°	9660
85°	9624



TEST NUMBER: P221785

CATALOG NUMBER: 9004-W2-[RW, RI]-LED3090-S-WT-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	636.9	19.6
10°-20°	456.4	14.0
20°-30°	352.2	10.8
30°-40°	97.6	3.0
40°-50°	18.9	0.6
50°-60°	19.4	0.6
60°-70°	20.1	0.6
70°-80°	18.0	0.6
80°-90°	7.6	0.2
90°-100°	7.6	0.2
100°-110°	18.0	0.6
110°-120°	20.1	0.6
120°-130°	19.4	0.6
130°-140°	18.9	0.6
140°-150°	97.6	3.0
150°-160°	352.2	10.8
160°-170°	456.4	14.0
170°-180°	636.9	19.6
0°-30°	1445.6	44.4
0°-40°	1543.2	47.4
0°-60°	1581.5	48.6
0°-90°	1627.1	50.0
90°-120°	45.6	1.4
90°-150°	181.5	5.6
90°-180°	1627.0	50.0
0°-180°	3254.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10903	
5°	8440	637
15°	1483	456
25°	757	352
35°	68	98
45°	23	19
55°	22	19
65°	20	20
75°	17	18
85°	7	7
90°	0	1
95°	7	7
105°	17	18
115°	20	20
125°	22	19
135°	23	19
145°	68	98
155°	757	352
165°	1483	456
175°	8440	637
180°	10903	



TEST NUMBER: P221785

CATALOG NUMBER: 9004-W2-[RW, RI]-LED3090-S-WT-L2-UNV

CANDELA DISTRIBUTION (FULL):

	0°
0°	10903.3
1°	10750.5
2°	10433.9
3°	9952.8
4°	9283.8
5°	8440.5
6°	7488.1
7°	6482.8
8°	5394.3
9°	4407.5
10°	3535.9
11°	2849.0
12°	2327.9
13°	1950.9
14°	1684.2
15°	1482.7
16°	1333.0
17°	1220.9
18°	1132.8
19°	1055.8
20°	985.0
22.5°	853.2
25°	757.1
26°	732.4
27°	711.5
28°	686.2
29°	631.4
30°	540.9
32.5°	260.0
35°	67.8
37.5°	43.7
40°	33.9
42.5°	25.3
45°	22.8
47.5°	22.2
50°	22.2
52.5°	21.6
55°	21.6
57.5°	21.6
60°	20.9
62.5°	20.9
65°	20.3
67.5°	19.7
70°	19.1
72.5°	18.5



TEST NUMBER: P221785

CATALOG NUMBER: 9004-W2-[RW, RI]-LED3090-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
75°	17.2
77.5°	16.0
80°	13.6
82.5°	11.1
85°	6.8
87.5°	3.1
90°	0.0
92.5°	3.1
95°	6.8
97.5°	11.1
100°	13.6
102.5°	16.0
105°	17.2
107.5°	18.5
110°	19.1
112.5°	19.7
115°	20.3
117.5°	20.9
120°	20.9
122.5°	21.6
125°	21.6
127.5°	21.6
130°	22.2
132.5°	22.2
135°	22.8
137.5°	25.3
140°	33.9
142.5°	43.7
145°	67.8
147.5°	260.0
150°	540.9
151°	631.4
152°	686.2
153°	711.5
154°	732.4
155°	757.1
157.5°	853.2
160°	985.0
161°	1055.8
162°	1132.8
163°	1220.9
164°	1333.0
165°	1482.7
166°	1684.2
167°	1950.9



TEST NUMBER: P221785

CATALOG NUMBER: 9004-W2-[RW, RI]-LED3090-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
168°	2327.9
169°	2849.0
170°	3535.9
171°	4407.5
172°	5394.3
173°	6482.8
174°	7488.1
175°	8440.5
176°	9283.8
177°	9952.8
178°	10433.9
179°	10750.5
180°	10903.3

(END OF REPORT)