

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P827971

Luminaire Tested: **OHBL-15HE-MFL-UNV-L935-CD-UPL15**

Issue Date: 5/3/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P827971  
REPORT IS A COMBINATION OF REPORTS P826109 AND G3-2310-221-10  
Test Lab: INNOVATION CENTER  
Issue Date: 5/3/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: OHBL-15HE-MFL-UNV-L935-CD-UPL15  
Description:  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1266.0 lumens  
Efficiency: N/A  
Efficacy: 122.9 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular w/ Sides (W: 3.78' x L: 1.67' x H: 0.17')  
CIE Type: Indirect

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P827971

CATALOG NUMBER: OHBL-15HE-MFL-UNV-L935-CD-UPL15

### Luminous Intensity Polar Plot





TEST NUMBER: P827971

CATALOG NUMBER: OHBL-15HE-MFL-UNV-L935-CD-UPL15

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0																
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	9	9	9	9	0																
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0																
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0																
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0																
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0																
6	55	44	36	31	47	38	31	27	26	22	19	15	13	11	5	4	4	4	4	4	0																
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0																
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0																
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	2	2	2	2	0																
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P827971

CATALOG NUMBER: OHBL-15HE-MFL-UNV-L935-CD-UPL15

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.2	0.3
90°-100°	121.4	9.6
100°-110°	420.5	33.2
110°-120°	361.3	28.5
120°-130°	173.4	13.7
130°-140°	86.7	6.8
140°-150°	50.3	4.0
150°-160°	29.3	2.3
160°-170°	15.2	1.2
170°-180°	4.6	0.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.2	0.3
90°-120°	903.2	71.3
90°-150°	1213.6	95.9
90°-180°	1263.0	99.8
0°-180°	1266.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	18	24	32	36	2
95°	23	60	89	118	138	83
105°	528	520	443	313	288	499
115°	363	363	367	365	358	367
125°	176	186	191	189	188	166
135°	104	108	110	112	112	83
145°	76	78	79	81	81	48
155°	61	62	63	63	64	29
165°	52	52	53	53	53	15
175°	48	48	48	48	48	5
180°	48	48	48	48	48	



TEST NUMBER: P827971

CATALOG NUMBER: OHBL-15HE-MFL-UNV-L935-CD-UPL15

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.5	18.3	24.2	31.7	35.8
92.5°	8.3	23.3	38.3	53.3	61.7
95°	23.3	60.0	89.2	118.3	137.5
97.5°	138.3	155.8	170.0	195.8	210.8
100°	280.8	303.3	249.2	261.7	267.5
102.5°	451.7	436.7	322.5	290.0	285.0
105°	527.5	520.0	443.3	313.3	287.5



TEST NUMBER: P827971

CATALOG NUMBER: OHBL-15HE-MFL-UNV-L935-CD-UPL15

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	424.2	430.0	422.5	407.5	392.5
115°	363.3	363.3	366.7	365.0	357.5
117.5°	311.7	310.0	313.3	311.7	310.0
120°	260.0	263.3	264.2	262.5	261.7
122.5°	215.0	221.7	225.8	223.3	222.5
125°	175.8	185.8	190.8	189.2	188.3
127.5°	150.0	155.8	162.5	162.5	160.8
130°	130.0	134.2	139.2	140.0	140.0
132.5°	115.8	119.2	123.3	124.2	125.0
135°	104.2	107.5	110.0	111.7	112.5
137.5°	95.8	97.5	100.8	101.7	102.5
140°	87.5	90.0	92.5	93.3	94.2
142.5°	81.7	83.3	85.0	86.7	86.7
145°	75.8	77.5	79.2	80.8	80.8
147.5°	71.7	73.3	75.0	75.0	75.8
150°	67.5	69.2	70.0	70.8	70.8
152.5°	64.2	65.0	66.7	66.7	67.5
155°	60.8	61.7	63.3	63.3	64.2
157.5°	58.3	59.2	60.0	60.8	60.8
160°	55.8	56.7	57.5	57.5	58.3
162.5°	54.2	55.0	55.0	55.8	55.8
165°	52.5	52.5	53.3	53.3	53.3
167.5°	50.8	50.8	51.7	51.7	52.5
170°	49.2	50.0	50.0	50.0	50.8
172.5°	48.3	48.3	49.2	49.2	49.2
175°	47.5	47.5	47.5	48.3	48.3
177.5°	46.7	47.5	47.5	47.5	47.5
180°	47.5	47.5	47.5	47.5	47.5



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	527.5	528.3	489.2	376.7	315.8
110°	486.7	490.8	469.2	426.7	375.0



(END OF REPORT)