

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P246983

Luminaire Tested: **203-SS-8LED3036-12-BK**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246983
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-6)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED3036-12-BK
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD BLACK
Light Source: (1) SORAA 3000K 95 CRI LED
SM16-07-36D-930-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 327.2 lumens
Efficiency: N/A
Efficacy: 42.0 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.54
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246983

CATALOG NUMBER: 203-SS-8LED3036-12-BK

Luminous Intensity Polar Plot





TEST NUMBER: P246983

CATALOG NUMBER: 203-SS-8LED3036-12-BK

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 115 | 113 | 111 | 109 | 112 | 111 | 109 | 107 | 107 | 105 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 96 | 96 | 96 | 96 |
| 2 | 111 | 107 | 104 | 102 | 109 | 106 | 103 | 100 | 102 | 100 | 98 | 100 | 98 | 96 | 97 | 95 | 94 | 93 | 93 | 93 | 93 |
| 3 | 107 | 102 | 99 | 96 | 105 | 101 | 98 | 95 | 99 | 96 | 94 | 96 | 94 | 92 | 94 | 92 | 91 | 89 | 89 | 89 | 89 |
| 4 | 104 | 98 | 94 | 91 | 102 | 97 | 93 | 90 | 95 | 92 | 89 | 93 | 91 | 88 | 92 | 89 | 87 | 86 | 86 | 86 | 86 |
| 5 | 100 | 94 | 90 | 87 | 99 | 93 | 89 | 86 | 92 | 88 | 86 | 90 | 87 | 85 | 89 | 86 | 84 | 83 | 83 | 83 | 83 |
| 6 | 97 | 91 | 86 | 83 | 96 | 90 | 86 | 83 | 89 | 85 | 83 | 87 | 84 | 82 | 86 | 84 | 81 | 80 | 80 | 80 | 80 |
| 7 | 94 | 88 | 83 | 80 | 93 | 87 | 83 | 80 | 86 | 82 | 80 | 85 | 82 | 79 | 84 | 81 | 79 | 78 | 78 | 78 | 78 |
| 8 | 91 | 85 | 80 | 77 | 90 | 84 | 80 | 77 | 83 | 79 | 77 | 82 | 79 | 77 | 81 | 78 | 76 | 75 | 75 | 75 | 75 |
| 9 | 89 | 82 | 78 | 75 | 88 | 81 | 77 | 75 | 81 | 77 | 74 | 80 | 76 | 74 | 79 | 76 | 74 | 73 | 73 | 73 | 73 |
| 10 | 86 | 79 | 75 | 72 | 85 | 79 | 75 | 72 | 78 | 74 | 72 | 78 | 74 | 72 | 77 | 74 | 72 | 71 | 71 | 71 | 71 |

AVERAGE LUMINANCE (cd/sqm):

| | 0° |
|-----|--------|
| 0° | 492047 |
| 5° | 474166 |
| 10° | 418828 |
| 15° | 318780 |
| 20° | 182453 |
| 25° | 69953 |
| 30° | 16692 |
| 35° | 5903 |
| 40° | 2254 |
| 45° | 1256 |
| 50° | 691 |
| 55° | 774 |
| 60° | 888 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P246983

CATALOG NUMBER: 203-SS-8LED3036-12-BK

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 87.7 | 26.8 |
| 10°-20° | 166.1 | 50.8 |
| 20°-30° | 63.9 | 19.5 |
| 30°-40° | 7.2 | 2.2 |
| 40°-50° | 1.4 | 0.4 |
| 50°-60° | 0.8 | 0.2 |
| 60°-70° | 0.1 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 317.7 | 97.1 |
| 0°-40° | 324.9 | 99.3 |
| 0°-60° | 327.1 | 100.0 |
| 0°-90° | 327.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 327.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 997 | |
| 5° | 957 | 88 |
| 15° | 624 | 166 |
| 25° | 128 | 64 |
| 35° | 10 | 7 |
| 45° | 2 | 1 |
| 55° | 1 | 1 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P246983

CATALOG NUMBER: 203-SS-8LED3036-12-BK

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 997.3 |
| 1° | 991.1 |
| 2° | 982.2 |
| 3° | 975.1 |
| 4° | 967.2 |
| 5° | 957.4 |
| 6° | 943.2 |
| 7° | 925.5 |
| 8° | 900.7 |
| 9° | 869.7 |
| 10° | 836.0 |
| 11° | 796.1 |
| 12° | 755.3 |
| 13° | 712.7 |
| 14° | 668.4 |
| 15° | 624.1 |
| 16° | 575.3 |
| 17° | 523.9 |
| 18° | 466.3 |
| 19° | 406.0 |
| 20° | 347.5 |
| 21° | 292.5 |
| 22° | 241.1 |
| 23° | 195.0 |
| 24° | 158.7 |
| 25° | 128.5 |
| 26° | 102.8 |
| 27° | 74.5 |
| 28° | 55.8 |
| 29° | 40.8 |
| 30° | 29.3 |
| 32.5° | 16.0 |
| 35° | 9.8 |
| 37.5° | 5.3 |
| 40° | 3.5 |
| 42.5° | 2.7 |
| 45° | 1.8 |
| 47.5° | 0.9 |
| 50° | 0.9 |
| 52.5° | 0.9 |
| 55° | 0.9 |
| 57.5° | 0.9 |
| 60° | 0.9 |
| 62.5° | 0.0 |
| 65° | 0.0 |



TEST NUMBER: P246983

CATALOG NUMBER: 203-SS-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|-----|
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)