

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-27

Luminaire Tested: **203-SS-8LED4010-12-BK-OSL**

Test Date: 04/06/18

Test Information

Test Method: LM-79-08
Report Number: G2-1802-569-27
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-27)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/06/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4010-12-BK-OSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD BLACK, OVERALL SPREAD LENS
Light Source: (1) SORAA 4000K 95 CRI 10°NSP LED
SM16-07-10D-940-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 285.7 lumens
Efficiency: N/A
Efficacy: 35.7 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): 12.0
Input Current (A_{in}): 0.709
Voltage Rise (V): NR
Power Factor: 0.9468
Total Harmonic Distortion (THDi): 27.5
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 9 HR
Ambient Temperature (°C): 25.1
Test Distance: 25 FT



TEST NUMBER: G2-1802-569-27
CATALOG NUMBER: 203-SS-8LED4010-12-BK-OSL

Luminous Intensity Polar Plot





TEST NUMBER: G2-1802-569-27

CATALOG NUMBER: 203-SS-8LED4010-12-BK-OSL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95
3	109	104	101	98	107	103	100	98	101	98	96	98	96	95	96	95	93	92
4	106	101	97	94	104	100	96	94	98	95	93	96	94	92	94	92	91	90
5	103	98	94	91	102	97	93	91	95	92	90	94	91	89	92	90	89	88
6	101	95	91	88	99	94	91	88	93	90	88	92	89	87	91	88	87	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	86	83	81	80
10	92	86	83	80	91	86	82	80	85	82	80	85	82	80	84	82	80	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	838745
5°	836996
10°	534557
15°	171623
20°	43054
25°	19598
30°	12534
35°	9637
40°	7085
45°	5582
50°	3838
55°	2581
60°	987
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: G2-1802-569-27

CATALOG NUMBER: 203-SS-8LED4010-12-BK-OSL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.0	49.0
10°-20°	108.4	37.9
20°-30°	18.6	6.5
30°-40°	9.8	3.4
40°-50°	6.1	2.1
50°-60°	2.7	0.9
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	266.9	93.4
0°-40°	276.8	96.9
0°-60°	285.6	100.0
0°-90°	285.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	285.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1700	
5°	1690	140
15°	336	108
25°	36	19
35°	16	10
45°	8	6
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: G2-1802-569-27

CATALOG NUMBER: 203-SS-8LED4010-12-BK-OSL

CANDELA DISTRIBUTION (FULL):

	0°
0°	1700
1°	1708
2°	1728
3°	1743
4°	1734
5°	1690
6°	1610
7°	1499
8°	1363
9°	1219
10°	1067
12.5°	678
15°	336
17.5°	148
20°	82
22.5°	52
25°	36
27.5°	27
30°	22
32.5°	18
35°	16
37.5°	13
40°	11
42.5°	9
45°	8
47.5°	7
50°	5
52.5°	4
55°	3
57.5°	2
60°	1
62.5°	0
65°	0
67.5°	0
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)