

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-28

Luminaire Tested: **203-SS-8LED4025-12-BK-DIFF**

Test Date: 04/06/18

Test Information

Test Method: LM-79-08
Report Number: G2-1802-569-28
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-28)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/06/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4025-12-BK-DIFF
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD BLACK, DIFFUSED LENS
Light Source: (1) SORAA 4000K 95 CRI 25°NFL LED
SM16-07-25D-940-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 267.7 lumens
Efficiency: N/A
Efficacy: 33.9 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.54
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): 12.0
Input Current (Ain): 0.693
Voltage Rise (V): NR
Power Factor: 0.9491
Total Harmonic Distortion (THDi): 26.9%
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 9 HR
Ambient Temperature (°C): 25.1
Test Distance: 25 FT



TEST NUMBER: G2-1802-569-28
CATALOG NUMBER: 203-SS-8LED4025-12-BK-DIFF

Luminous Intensity Polar Plot





TEST NUMBER: G2-1802-569-28

CATALOG NUMBER: 203-SS-8LED4025-12-BK-DIFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82
5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	79	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69
9	84	76	71	68	83	76	71	68	75	70	67	74	70	67	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	64	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	359674
5°	332322
10°	266026
15°	193587
20°	128636
25°	81113
30°	47286
35°	24092
40°	11593
45°	4884
50°	2303
55°	860
60°	987
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: G2-1802-569-28

CATALOG NUMBER: 203-SS-8LED4025-12-BK-DIFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.5	22.2
10°-20°	104.3	38.9
20°-30°	69.3	25.9
30°-40°	26.8	10.0
40°-50°	6.3	2.4
50°-60°	1.3	0.5
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	233.1	87.1
0°-40°	259.9	97.1
0°-60°	267.6	100.0
0°-90°	267.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	267.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	729	
5°	671	60
15°	379	104
25°	149	69
35°	40	27
45°	7	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: G2-1802-569-28

CATALOG NUMBER: 203-SS-8LED4025-12-BK-DIFF

CANDELA DISTRIBUTION (FULL):

	0°
0°	729
1°	724
2°	715
3°	704
4°	689
5°	671
6°	649
7°	624
8°	595
9°	564
10°	531
12.5°	454
15°	379
17.5°	309
20°	245
22.5°	192
25°	149
27.5°	113
30°	83
32.5°	58
35°	40
37.5°	27
40°	18
42.5°	11
45°	7
47.5°	5
50°	3
52.5°	2
55°	1
57.5°	1
60°	1
62.5°	0
65°	0
67.5°	0
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)