

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P247013

Luminaire Tested: **203-SS-8LED2710-12-CS-LSL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247013  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-37)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-SS-8LED2710-12-CS-LSL  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 10 DEGREE SPOT OPTIC,  
REGRESSED HOOD SILVER, LINEAR SPREAD LENS  
Light Source: (1) SORAA 2700K 95 CRI 10° NSP LED  
SM16-07-10D-927-03  
Ballast/Driver: CHROMA POWER SUPPLY IN0004

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 230.6 lumens  
Efficiency: N/A  
Efficacy: 30.7 lumens/watt  
Spacing Criteria (0/90/45): 0.21 / 0.89 / 0.26  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247013  
CATALOG NUMBER: 203-SS-8LED2710-12-CS-LSL

### Luminous Intensity Polar Plot





TEST NUMBER: P247013

CATALOG NUMBER: 203-SS-8LED2710-12-CS-LSL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95	95	95	95		
2	110	105	102	99	107	104	100	98	100	98	96	97	95	94	95	93	92	90	90	90	90	90	90	90		
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	85	85	85	85	85	85	85		
4	101	94	90	86	99	93	89	86	91	88	85	89	86	84	88	85	83	81	81	81	81	81	81	81		
5	97	90	85	81	95	89	84	81	87	83	80	86	82	80	84	81	79	78	78	78	78	78	78	78		
6	93	86	81	77	92	85	80	77	84	80	77	82	79	76	81	78	76	74	74	74	74	74	74	74		
7	90	82	77	74	89	82	77	74	80	76	73	79	76	73	78	75	72	71	71	71	71	71	71	71		
8	87	79	74	71	86	78	74	70	77	73	70	76	73	70	76	72	70	68	68	68	68	68	68	68		
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	66	66	66	66	66	66		
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64	64	64	64	64	64	64		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	540497	540497	540497
5°	334997	476543	354906
10°	73195	364972	77303
15°	41476	477021	41476
20°	22052	571352	21579
25°	14426	332945	14916
30°	11451	80613	11964
35°	9336	19274	9878
40°	8244	12946	8244
45°	6977	11443	6977
50°	5603	9134	5603
55°	4731	7053	4731
60°	2664	3651	2664
65°	2101	2101	1051
70°	1298	1298	1298
75°	1716	1716	1716
80°	0	0	0
85°	0	0	0



TEST NUMBER: P247013

CATALOG NUMBER: 203-SS-8LED2710-12-CS-LSL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.8	26.8
10°-20°	79.1	34.3
20°-30°	56.6	24.5
30°-40°	14.6	6.4
40°-50°	9.9	4.3
50°-60°	5.9	2.6
60°-70°	1.8	0.8
70°-80°	0.8	0.4
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	197.5	85.6
0°-40°	212.1	92.0
0°-60°	228.0	98.9
0°-90°	230.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	230.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1096	1096	1096	1096	1096	
5°	676	808	962	851	717	43
15°	81	103	934	110	81	23
25°	26	37	612	38	27	13
35°	16	19	32	19	16	10
45°	10	13	16	13	10	8
55°	6	6	8	6	6	5
65°	2	2	2	2	1	2
75°	1	1	1	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P247013

CATALOG NUMBER: 203-SS-8LED2710-12-CS-LSL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1095.5	1095.5	1095.5	1095.5	1095.5	1095.5	1095.5	1095.5	1095.5
1°	1072.6	1074.5	1076.3	1081.8	1087.2	1085.4	1085.4	1087.2	1081.8
2°	1010.6	1030.6	1042.5	1058.0	1069.9	1066.2	1057.1	1050.7	1036.1
3°	926.6	958.5	984.1	1022.4	1043.4	1035.2	1011.5	989.6	965.8
4°	814.3	856.3	906.5	973.1	1006.0	991.4	943.9	896.5	857.2
5°	676.4	732.1	807.9	911.1	962.2	934.8	850.8	774.1	716.6
6°	511.2	587.9	688.3	830.7	903.8	858.1	736.7	627.2	560.5
7°	359.7	435.4	566.0	752.2	841.7	783.3	613.5	471.0	398.9
8°	240.1	302.2	443.7	672.8	788.7	705.7	489.3	330.5	276.6
9°	178.0	210.9	338.7	606.2	749.5	638.1	380.7	232.8	197.2
10°	146.1	161.6	256.5	552.3	728.5	585.2	291.2	174.4	154.3
12.5°	106.8	113.2	144.2	453.7	770.5	486.6	161.6	116.8	108.6
15°	81.2	84.9	103.2	387.1	933.9	422.7	109.5	88.5	81.2
17.5°	59.3	64.8	82.2	324.1	1088.2	362.4	85.8	66.6	59.3
20°	42.0	47.5	63.9	241.9	1088.2	281.2	66.6	48.4	41.1
22.5°	32.9	35.6	49.3	154.3	894.6	181.7	51.1	35.6	32.0
25°	26.5	28.3	37.4	93.1	611.6	106.8	38.3	28.3	27.4
27.5°	22.8	23.7	30.1	61.2	327.7	66.6	30.1	24.6	23.7
30°	20.1	21.0	24.6	40.2	141.5	41.1	24.6	21.9	21.0
32.5°	17.3	19.2	21.0	29.2	59.3	29.2	21.9	19.2	18.3
35°	15.5	17.3	19.2	22.8	32.0	22.8	19.2	17.3	16.4
37.5°	13.7	15.5	17.3	20.1	24.6	20.1	17.3	16.4	14.6
40°	12.8	13.7	15.5	17.3	20.1	18.3	15.5	14.6	12.8
42.5°	11.0	12.8	13.7	15.5	18.3	15.5	14.6	12.8	11.9
45°	10.0	11.0	12.8	13.7	16.4	14.6	12.8	11.9	10.0
47.5°	9.1	10.0	11.9	11.9	14.6	12.8	11.9	10.0	9.1
50°	7.3	9.1	10.0	11.0	11.9	11.0	10.0	8.2	7.3
52.5°	6.4	7.3	9.1	9.1	10.0	9.1	8.2	7.3	6.4
55°	5.5	6.4	6.4	7.3	8.2	7.3	6.4	5.5	5.5
57.5°	4.6	4.6	5.5	5.5	5.5	5.5	4.6	4.6	3.7
60°	2.7	3.7	3.7	3.7	3.7	3.7	3.7	2.7	2.7
62.5°	1.8	1.8	1.8	2.7	2.7	1.8	1.8	1.8	1.8
65°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	0.9
67.5°	0.9	0.9	1.8	1.8	1.8	1.8	0.9	0.9	0.9
70°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
72.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
75°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
77.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0	0.0
80°	0.0	0.0	0.9	0.9	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)