

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P247034

Luminaire Tested: **203-SS-8LED2736-12-CS-LVR**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247034  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-46)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-SS-8LED2736-12-CS-LVR  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 36 DEGREE WIDE OPTIC,  
REGRESSED HOOD SILVER, HEX CELL LOUVER  
Light Source: (1) SORAA 2700K 90 CRI LED  
SM16-07-36D-927-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 229.9 lumens  
Efficiency: N/A  
Efficacy: 30.2 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.48  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247034  
CATALOG NUMBER: 203-SS-8LED2736-12-CS-LVR

### Luminous Intensity Polar Plot





TEST NUMBER: P247034

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LVR

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100		
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96	96	96	96		
2	111	107	104	102	109	106	103	101	103	100	99	100	98	96	97	96	95	93	93	93	93	93	93	93		
3	107	103	99	96	106	101	98	95	99	96	94	97	94	93	95	93	91	90	90	90	90	90	90	90		
4	104	99	95	92	102	98	94	91	96	92	90	94	91	89	92	90	88	87	87	87	87	87	87	87		
5	101	95	91	88	99	94	90	87	92	89	87	91	88	86	90	87	85	84	84	84	84	84	84	84		
6	98	92	87	84	97	91	87	84	89	86	83	88	85	83	87	84	82	81	81	81	81	81	81	81		
7	95	88	84	81	94	88	84	81	87	83	81	86	83	80	85	82	80	79	79	79	79	79	79	79		
8	92	86	81	79	91	85	81	78	84	81	78	83	80	78	82	80	77	76	76	76	76	76	76	76		
9	90	83	79	76	89	83	79	76	82	78	76	81	78	75	80	77	75	74	74	74	74	74	74	74		
10	87	81	76	74	87	80	76	74	80	76	73	79	76	73	78	75	73	72	72	72	72	72	72	72		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	43555
5°	39834
10°	31787
15°	21636
20°	10831
25°	3729
30°	1145
35°	548
40°	296
45°	188
50°	69
55°	77
60°	88
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P247034

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LVR

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.4	31.1
10°-20°	112.8	49.1
20°-30°	36.0	15.7
30°-40°	6.2	2.7
40°-50°	2.1	0.9
50°-60°	0.8	0.4
60°-70°	0.6	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	220.2	95.8
0°-40°	226.4	98.5
0°-60°	229.3	99.8
0°-90°	229.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	229.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	883	
5°	804	71
15°	424	113
25°	68	36
35°	9	6
45°	3	2
55°	1	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P247034

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LVR

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	882.8
1°	872.7
2°	856.3
3°	840.8
4°	824.3
5°	804.3
6°	779.6
7°	750.4
8°	714.8
9°	676.4
10°	634.5
11°	590.6
12°	548.6
13°	506.7
14°	464.7
15°	423.6
16°	380.7
17°	335.0
18°	291.2
19°	247.4
20°	206.3
21°	169.8
22°	136.9
23°	109.5
24°	86.7
25°	68.5
26°	52.0
27°	41.1
28°	32.0
29°	24.6
30°	20.1
32.5°	12.8
35°	9.1
37.5°	6.4
40°	4.6
42.5°	3.7
45°	2.7
47.5°	1.8
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.0



TEST NUMBER: P247034

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)