

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P277774

Luminaire Tested: **203-SS-8LED3036-12-BK-LVR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P277774
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-34)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED3036-12-BK-LVR
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 36 DEGREE WIDE OPTIC, REGRESSED HOOD BLACK, HEX CELL LOUVER
Light Source: (1) SORAA 3000K 95 CRI LED SM16-07-36D-930-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 446.9 lumens
Efficiency: N/A
Efficacy: 28.6 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.48
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 15.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P277774
CATALOG NUMBER: 203-SS-8LED3036-12-BK-LVR

Luminous Intensity Polar Plot





TEST NUMBER: P277774

CATALOG NUMBER: 203-SS-8LED3036-12-BK-LVR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	101	98	95	93	93	91	88	86	78	76	75	65	65	64	54	54	53	48				
2	95	90	86	82	88	84	80	77	73	70	68	62	61	59	53	52	51	47				
3	90	83	78	74	83	78	74	70	68	65	63	59	57	56	51	50	49	45				
4	85	77	72	68	79	73	68	64	64	61	58	57	54	53	49	48	47	44				
5	81	72	67	62	75	68	63	60	61	57	55	54	52	50	48	46	45	42				
6	77	68	62	58	72	65	60	56	58	54	52	52	49	48	46	45	43	41				
7	73	64	58	54	69	61	56	53	55	52	49	50	47	45	45	43	42	40				
8	70	61	55	51	66	58	53	50	53	49	47	48	46	44	44	42	41	39				
9	67	58	52	49	63	55	51	47	51	47	45	46	44	42	42	41	39	38				
10	64	55	50	46	61	53	48	45	49	45	43	45	42	40	41	39	38	37				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	435605
5°	393834
10°	314873
15°	211005
20°	108001
25°	35712
30°	10084
35°	4276
40°	2254
45°	1256
50°	691
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P277774

CATALOG NUMBER: 203-SS-8LED3036-12-BK-LVR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.7	15.8
10°-20°	111.0	24.8
20°-30°	35.2	7.9
30°-40°	5.0	1.1
40°-50°	1.4	0.3
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.1	0.0
130°-140°	1.4	0.3
140°-150°	5.0	1.1
150°-160°	35.2	7.9
160°-170°	111.0	24.8
170°-180°	70.7	15.8
0°-30°	216.9	48.5
0°-40°	221.9	49.7
0°-60°	223.4	50.0
0°-90°	223.4	50.0
90°-120°	0.0	0.0
90°-150°	6.5	1.5
90°-180°	223.0	49.9
0°-180°	446.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	883	
5°	795	71
15°	413	111
25°	66	35
35°	7	5
45°	2	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	2	1
145°	7	5
155°	66	35
165°	413	111
175°	795	71
180°	883	



TEST NUMBER: P277774

CATALOG NUMBER: 203-SS-8LED3036-12-BK-LVR

CANDELA DISTRIBUTION (FULL):

	0°
0°	882.9
1°	873.2
2°	855.5
3°	836.0
4°	816.5
5°	795.2
6°	770.4
7°	742.0
8°	706.5
9°	668.4
10°	628.5
11°	585.1
12°	539.9
13°	496.4
14°	453.9
15°	413.1
16°	372.3
17°	330.7
18°	288.1
19°	246.4
20°	205.7
21°	168.4
22°	136.5
23°	109.0
24°	84.2
25°	65.6
26°	51.4
27°	38.1
28°	30.1
29°	22.2
30°	17.7
32.5°	10.6
35°	7.1
37.5°	4.4
40°	3.5
42.5°	2.7
45°	1.8
47.5°	0.9
50°	0.9
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0



TEST NUMBER: P277774

CATALOG NUMBER: 203-SS-8LED3036-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.9
132.5°	0.9
135°	1.8
137.5°	2.7
140°	3.5
142.5°	4.4
145°	7.1
147.5°	10.6
150°	17.7
151°	22.2
152°	30.1
153°	38.1
154°	51.4
155°	65.6
156°	84.2
157°	109.0
158°	136.5
159°	168.4
160°	205.7
161°	246.4



TEST NUMBER: P277774

CATALOG NUMBER: 203-SS-8LED3036-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	0°
162°	288.1
163°	330.7
164°	372.3
165°	413.1
166°	453.9
167°	496.4
168°	539.9
169°	585.1
170°	628.5
171°	668.4
172°	706.5
173°	742.0
174°	770.4
175°	795.2
176°	816.5
177°	836.0
178°	855.5
179°	873.2
180°	882.9

(END OF REPORT)