

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P277803

Luminaire Tested: **203-SS-8LED4036-12-BK-LSL**

Test Date: 04/06/18

Test Information

Test Method: LM-79-08
Report Number: P277803
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-33)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/06/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4036-12-BK-LSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD BLACK, LINEAR SPREAD LENS
Light Source: (1) SORAA 4000K 95 CRI LED
SM16-07-36D-940-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 611.3 lumens
Efficiency: N/A
Efficacy: 39.4 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.02 / 0.74
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 15.5
Input Voltage (V): 12.0
Input Current (A_{in}): 0.681
Voltage Rise (V): NR
Power Factor: 0.9907
Total Harmonic Distortion (THDi): 27.5%
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): 24.9
Test Distance: 25 FT



TEST NUMBER: P277803
CATALOG NUMBER: 203-SS-8LED4036-12-BK-LSL

Luminous Intensity Polar Plot





TEST NUMBER: P277803

CATALOG NUMBER: 203-SS-8LED4036-12-BK-LSL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		56	56	56	50
1	100	97	94	92	93	90	88	85	77	75	74		65	64	63		54	53	53	47
2	94	88	84	80	87	82	79	75	71	68	66		61	59	57		51	50	49	45
3	88	81	76	71	82	76	71	67	66	63	60		57	55	53		49	47	46	42
4	83	75	69	64	77	70	65	61	62	58	55		54	51	49		46	45	43	40
5	78	69	63	58	73	65	59	55	58	54	50		51	48	46		44	42	41	38
6	73	64	58	53	69	60	55	51	54	50	47		48	45	43		42	40	38	36
7	69	60	53	49	65	56	51	47	51	46	43		45	42	40		40	38	36	34
8	65	56	49	45	61	53	47	44	48	44	41		43	40	38		38	36	34	32
9	62	52	46	42	58	50	44	41	45	41	38		41	38	35		37	34	33	31
10	59	49	43	39	55	47	42	38	43	39	36		39	36	33		35	33	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	236822	236822	236822
5°	226336	242679	254566
10°	192881	237971	273040
15°	140976	218616	277867
20°	77706	175365	254121
25°	31574	117587	207955
30°	10255	63237	157808
35°	4818	21683	90346
40°	2576	6441	32203
45°	1395	2791	6977
50°	768	1535	2303
55°	860	860	860
60°	987	987	987
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P277803

CATALOG NUMBER: 203-SS-8LED4036-12-BK-LSL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.2	7.6
10°-20°	114.5	18.7
20°-30°	99.4	16.3
30°-40°	39.3	6.4
40°-50°	5.0	0.8
50°-60°	1.1	0.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.1	0.0
120°-130°	1.1	0.2
130°-140°	5.0	0.8
140°-150°	39.3	6.4
150°-160°	99.4	16.3
160°-170°	114.5	18.7
170°-180°	46.2	7.6
0°-30°	260.1	42.5
0°-40°	299.4	49.0
0°-60°	305.5	50.0
0°-90°	305.6	50.0
90°-120°	0.1	0.0
90°-150°	45.6	7.5
90°-180°	306.0	50.1
0°-180°	611.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	480	480	480	480	480	
5°	457	470	490	509	514	41
15°	276	324	428	514	544	73
25°	58	85	216	348	382	29
35°	8	11	36	114	150	5
45°	2	3	4	8	10	2
55°	1	1	1	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	1	1	1	1	1	1
135°	2	3	4	8	10	2
145°	8	11	36	114	150	5
155°	58	85	216	348	382	29
165°	276	324	428	514	544	73
175°	457	470	490	509	514	41
180°	480	480	480	480	480	



TEST NUMBER: P277803

CATALOG NUMBER: 203-SS-8LED4036-12-BK-LSL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	480	480	480	480	480
1°	477	478	480	482	483
2°	473	476	481	486	488
3°	469	475	484	493	497
4°	464	473	488	500	506
5°	457	470	490	509	514
6°	448	465	492	514	522
7°	435	458	492	519	530
8°	421	447	487	523	539
9°	404	435	482	526	542
10°	385	420	475	527	545
11°	364	404	469	526	547
12°	344	386	463	525	548
13°	322	367	452	523	548
14°	300	346	440	519	548
15°	276	324	428	514	544
16°	250	301	414	509	537
17°	225	278	398	499	529
18°	198	250	378	485	514
19°	174	223	357	469	499
20°	148	196	334	452	484
21°	124	170	313	433	468
22°	103	143	292	415	448
23°	86	120	266	397	426
24°	71	101	241	375	403
25°	58	85	216	348	382
26°	48	71	193	324	361
27°	38	58	170	299	339
28°	30	47	149	277	317
29°	24	37	129	249	296
30°	18	30	111	227	277
32.5°	11	17	67	175	214
35°	8	11	36	114	150
37.5°	5	7	18	64	81
40°	4	5	10	30	50
42.5°	3	4	6	14	20
45°	2	3	4	8	10
47.5°	2	2	2	4	5
50°	1	1	2	2	3
52.5°	1	1	1	2	2
55°	1	1	1	1	1
57.5°	1	1	1	1	1
60°	1	1	1	1	1
62.5°	0	0	0	0	0
65°	0	0	0	0	0



TEST NUMBER: P277803

CATALOG NUMBER: 203-SS-8LED4036-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
67.5°	0	0	0	0	0
70°	0	0	0	0	0
72.5°	0	0	0	0	0
75°	0	0	0	0	0
77.5°	0	0	0	0	0
80°	0	0	0	0	0
82.5°	0	0	0	0	0
85°	0	0	0	0	0
87.5°	0	0	0	0	0
90°	0	0	0	0	0
92.5°	0	0	0	0	0
95°	0	0	0	0	0
97.5°	0	0	0	0	0
100°	0	0	0	0	0
102.5°	0	0	0	0	0
105°	0	0	0	0	0
107.5°	0	0	0	0	0
110°	0	0	0	0	0
112.5°	0	0	0	0	0
115°	0	0	0	0	0
117.5°	0	0	0	0	0
120°	1	1	1	1	1
122.5°	1	1	1	1	1
125°	1	1	1	1	1
127.5°	1	1	1	2	2
130°	1	1	2	2	3
132.5°	2	2	2	4	5
135°	2	3	4	8	10
137.5°	3	4	6	14	20
140°	4	5	10	30	50
142.5°	5	7	18	64	81
145°	8	11	36	114	150
147.5°	11	17	67	175	214
150°	18	30	111	227	277
151°	24	37	129	249	296
152°	30	47	149	277	317
153°	38	58	170	299	339
154°	48	71	193	324	361
155°	58	85	216	348	382
156°	71	101	241	375	403
157°	86	120	266	397	426
158°	103	143	292	415	448
159°	124	170	313	433	468
160°	148	196	334	452	484
161°	174	223	357	469	499



TEST NUMBER: P277803

CATALOG NUMBER: 203-SS-8LED4036-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
162°	198	250	378	485	514
163°	225	278	398	499	529
164°	250	301	414	509	537
165°	276	324	428	514	544
166°	300	346	440	519	548
167°	322	367	452	523	548
168°	344	386	463	525	548
169°	364	404	469	526	547
170°	385	420	475	527	545
171°	404	435	482	526	542
172°	421	447	487	523	539
173°	435	458	492	519	530
174°	448	465	492	514	522
175°	457	470	490	509	514
176°	464	473	488	500	506
177°	469	475	484	493	497
178°	473	476	481	486	488
179°	477	478	480	482	483
180°	480	480	480	480	480

(END OF REPORT)