

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P247030

Luminaire Tested: **203-SS-8LED2736-12-BK-OSL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P247030
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-35)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED2736-12-BK-OSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD BLACK, OVERALL SPREAD LENS
Light Source: (1) SORAA 2700K 95 CRI LED
SM16-07-36D-927-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 308.4 lumens
Efficiency: N/A
Efficacy: 40.0 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.57 / 0.56
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247030
CATALOG NUMBER: 203-SS-8LED2736-12-BK-OSL

Luminous Intensity Polar Plot





TEST NUMBER: P247030

CATALOG NUMBER: 203-SS-8LED2736-12-BK-OSL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	109	112	110	108	107	106	105	104		103	101	100		99	98	98	96
2	110	107	103	101	108	105	102	99	102	99	97		99	97	95		96	95	93	92
3	106	101	97	94	105	100	96	94	98	95	92		95	93	91		93	91	89	88
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90	88	86	84
5	99	93	88	85	98	92	88	84	90	86	84		89	85	83		87	84	82	81
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84	81	79	78
7	92	85	81	77	91	85	80	77	84	80	77		82	79	76		81	78	76	75
8	89	82	77	74	88	82	77	74	81	77	74		80	76	74		79	76	73	72
9	86	79	74	71	86	79	74	71	78	74	71		77	73	71		76	73	71	70
10	84	76	72	69	83	76	72	69	75	71	69		74	71	68		74	71	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	419767
5°	401015
10°	344381
15°	258304
20°	170639
25°	92926
30°	37430
35°	11022
40°	4122
45°	1884
50°	691
55°	774
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P247030

CATALOG NUMBER: 203-SS-8LED2736-12-BK-OSL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.4	23.8
10°-20°	138.1	44.8
20°-30°	79.3	25.7
30°-40°	14.6	4.7
40°-50°	2.2	0.7
50°-60°	0.7	0.2
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	290.8	94.3
0°-40°	305.4	99.0
0°-60°	308.4	100.0
0°-90°	308.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	308.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	851	
5°	810	73
15°	506	138
25°	171	79
35°	18	15
45°	3	2
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P247030

CATALOG NUMBER: 203-SS-8LED2736-12-BK-OSL

CANDELA DISTRIBUTION (FULL):

0°	
0°	850.8
1°	844.4
2°	836.2
3°	828.0
4°	819.8
5°	809.7
6°	794.2
7°	773.2
8°	748.6
9°	718.4
10°	687.4
11°	653.6
12°	617.1
13°	580.6
14°	542.3
15°	505.7
16°	469.2
17°	433.6
18°	398.0
19°	361.5
20°	325.0
21°	290.3
22°	258.3
23°	226.4
24°	197.2
25°	170.7
26°	147.0
27°	124.2
28°	102.2
29°	82.2
30°	65.7
32.5°	32.9
35°	18.3
37.5°	10.0
40°	6.4
42.5°	3.7
45°	2.7
47.5°	1.8
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.0
62.5°	0.0
65°	0.0



TEST NUMBER: P247030
CATALOG NUMBER: 203-SS-8LED2736-12-BK-OSL

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)