

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P827652

Luminaire Tested: **OHBL-12HE-NL-UNV-L930-CD-UPL18**

Issue Date: 5/3/2024



Test Information

Test Method: LM-79-08
Report Number: P827652
REPORT IS A COMBINATION OF REPORTS P826147 AND G3-2310-221-8
Test Lab: INNOVATION CENTER
Issue Date: 5/3/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: OHBL-12HE-NL-UNV-L930-CD-UPL18
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1446.8 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular w/ Sides (W: 3.78' x L: 1.67' x H: 0.1')
CIE Type: Indirect

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P827652

CATALOG NUMBER: OHBL-12HE-NL-UNV-L930-CD-UPL18

Luminous Intensity Polar Plot





TEST NUMBER: P827652

CATALOG NUMBER: OHBL-12HE-NL-UNV-L930-CD-UPL18

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0																
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	9	9	9	9	0																
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0																
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0																
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0																
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0																
6	55	44	36	31	47	38	31	27	26	22	19	15	13	11	5	4	4	4	4	4	0																
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0																
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0																
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	2	2	2	2	0																
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P827652

CATALOG NUMBER: OHBL-12HE-NL-UNV-L930-CD-UPL18

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.6	0.3
90°-100°	138.4	9.6
100°-110°	480.7	33.2
110°-120°	413.0	28.5
120°-130°	198.3	13.7
130°-140°	99.1	6.8
140°-150°	57.5	4.0
150°-160°	33.6	2.3
160°-170°	17.4	1.2
170°-180°	5.3	0.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.6	0.3
90°-120°	1032.0	71.3
90°-150°	1386.9	95.9
90°-180°	1443.0	99.7
0°-180°	1446.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	20	28	36	40	2
95°	31	66	104	135	154	97
105°	599	593	506	356	329	568
115°	415	420	419	414	413	418
125°	202	212	217	217	215	190
135°	120	122	126	128	128	95
145°	87	89	91	92	92	55
155°	70	71	72	73	73	33
165°	60	61	61	61	61	17
175°	54	54	55	55	55	5
180°	54	54	54	54	54	



TEST NUMBER: P827652

CATALOG NUMBER: OHBL-12HE-NL-UNV-L930-CD-UPL18

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.2	20.2	27.5	36.4	40.4
92.5°	10.5	26.7	44.5	61.4	67.9
95°	30.7	66.3	104.3	135.0	154.4
97.5°	157.6	172.2	192.4	228.0	240.9
100°	325.0	341.1	286.2	299.9	304.7
102.5°	508.4	507.6	367.0	331.4	326.6
105°	599.0	593.3	506.0	356.5	329.0



TEST NUMBER: P827652

CATALOG NUMBER: OHBL-12HE-NL-UNV-L930-CD-UPL18

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.6	489.8	480.2	467.2	447.0
115°	414.7	419.5	418.7	413.9	413.1
117.5°	353.2	355.7	357.3	355.7	356.5
120°	295.0	300.7	303.9	301.5	299.9
122.5°	246.5	253.8	257.9	255.4	253.8
125°	202.1	211.8	217.4	216.6	215.0
127.5°	171.4	178.6	185.9	185.1	183.5
130°	148.7	154.4	159.2	160.0	160.9
132.5°	133.4	135.8	140.6	141.5	143.1
135°	119.6	122.1	126.1	127.7	128.5
137.5°	109.1	111.6	114.8	116.4	117.2
140°	100.2	102.7	105.1	106.7	107.5
142.5°	93.0	95.4	97.8	98.6	99.4
145°	87.3	88.9	91.3	92.2	92.2
147.5°	81.6	83.3	84.9	86.5	86.5
150°	76.8	78.4	80.0	80.8	81.6
152.5°	73.6	74.4	76.0	76.8	76.8
155°	69.5	71.1	71.9	72.8	72.8
157.5°	67.1	67.9	68.7	69.5	69.5
160°	64.7	64.7	65.5	66.3	66.3
162.5°	62.2	62.2	63.0	63.9	63.9
165°	59.8	60.6	60.6	61.4	61.4
167.5°	58.2	58.2	59.0	59.0	59.8
170°	56.6	56.6	57.4	57.4	57.4
172.5°	55.0	55.8	55.8	55.8	55.8
175°	54.2	54.2	55.0	55.0	55.0
177.5°	53.4	54.2	54.2	54.2	54.2
180°	54.2	54.2	54.2	54.2	54.2



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	604.6	604.6	557.8	433.3	362.9
110°	553.7	560.2	535.9	487.4	431.6



(END OF REPORT)