

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P246973

Luminaire Tested: **203-SS-8LED3025-12-BK**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246973  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-SS-8LED3025-12-BK  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD BLACK  
Light Source: (1) SORAA 3000K 95 CRI 25°NFL LED SM16-07-25D-930-03  
Ballast/Driver: CHROMA POWER SUPPLY IN0004

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 331.8 lumens  
Efficiency: N/A  
Efficacy: 42.0 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.33  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246973

CATALOG NUMBER: 203-SS-8LED3025-12-BK

### Luminous Intensity Polar Plot





TEST NUMBER: P246973

CATALOG NUMBER: 203-SS-8LED3025-12-BK

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	105	104	103	102	102	100	100	99	99	97	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	100	101	99	98	98	98	97	96	96	95	95	95	95
3	109	104	101	98	107	103	100	98	101	98	96	96	98	96	95	95	96	95	93	93	92	92	92	92
4	106	101	97	94	104	100	96	94	98	95	93	93	96	94	92	92	94	92	91	91	90	90	90	90
5	103	97	94	91	102	97	93	91	95	92	90	90	94	91	89	89	92	90	88	88	87	87	87	87
6	100	95	91	88	99	94	90	88	93	90	87	87	91	89	87	87	90	88	86	86	85	85	85	85
7	98	92	88	85	97	91	88	85	90	87	85	85	89	87	84	84	88	86	84	84	83	83	83	83
8	96	90	86	83	95	89	86	83	88	85	83	83	87	85	82	82	87	84	82	82	81	81	81	81
9	93	87	84	81	93	87	83	81	86	83	81	81	85	83	81	81	85	82	80	80	79	79	79	79
10	91	85	82	79	91	85	81	79	84	81	79	79	84	81	79	79	83	81	79	79	78	78	78	78

**AVERAGE LUMINANCE (cd/sqm):**

0°	
0°	1119232
5°	893457
10°	492975
15°	238179
20°	116822
25°	49212
30°	11109
35°	4276
40°	2254
45°	1256
50°	691
55°	774
60°	888
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246973

CATALOG NUMBER: 203-SS-8LED3025-12-BK

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.9	43.7
10°-20°	135.7	40.9
20°-30°	43.6	13.1
30°-40°	5.2	1.6
40°-50°	1.4	0.4
50°-60°	0.8	0.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.2	97.7
0°-40°	329.4	99.3
0°-60°	331.6	100.0
0°-90°	331.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	331.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2268	
5°	1804	145
15°	466	136
25°	90	44
35°	7	5
45°	2	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P246973

CATALOG NUMBER: 203-SS-8LED3025-12-BK

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2268.5
1°	2237.5
2°	2171.9
3°	2077.1
4°	1951.2
5°	1804.0
6°	1644.4
7°	1479.6
8°	1310.2
9°	1143.6
10°	984.0
12.5°	661.3
15°	466.3
17.5°	330.7
20°	222.5
22.5°	143.6
25°	90.4
27.5°	45.2
30°	19.5
32.5°	11.5
35°	7.1
37.5°	4.4
40°	3.5
42.5°	2.7
45°	1.8
47.5°	0.9
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)