

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-39

Luminaire Tested: **203-SS-8LED4010-12-CS-OSL**

Test Date: 04/05/18

Test Information

Test Method: LM-79-08
Report Number: G2-1802-569-39
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-39)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/05/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4010-12-CS-OSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD SILVER, OVERALL SPREAD LENS
Light Source: (1) SORAA 4000K 95 CRI 10° NSP LED
SM16-07-10D-940-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 291.1 lumens
Efficiency: N/A
Efficacy: 38.8 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): 12.0
Input Current (Ain): 0.656
Voltage Rise (V): NR
Power Factor: 0.9482
Total Harmonic Distortion (THDi): 25.7
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 9 HR
Ambient Temperature (°C): 25.0
Test Distance: 25 FT



TEST NUMBER: G2-1802-569-39
CATALOG NUMBER: 203-SS-8LED4010-12-CS-OSL

Luminous Intensity Polar Plot





TEST NUMBER: G2-1802-569-39

CATALOG NUMBER: 203-SS-8LED4010-12-CS-OSL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	107	107	105	104	104	103	102	101	101	100	99	98	98	96	96	96	96
2	111	107	104	102	109	106	103	101	103	100	99	99	100	98	96	96	97	96	94	94	93	93	93	93
3	107	103	99	96	106	101	98	95	99	96	94	94	97	94	93	93	95	93	91	91	90	90	90	90
4	104	99	95	92	103	98	94	91	96	93	90	90	94	91	89	89	92	90	88	88	87	87	87	87
5	101	95	91	88	100	94	91	88	93	89	87	87	91	88	86	86	90	87	86	86	84	84	84	84
6	98	92	88	85	97	91	88	85	90	87	84	84	89	86	84	84	88	85	83	83	82	82	82	82
7	96	89	85	82	95	89	85	82	88	84	82	82	87	84	81	81	86	83	81	81	80	80	80	80
8	93	87	83	80	92	86	83	80	86	82	80	80	85	82	79	79	84	81	79	79	78	78	78	78
9	91	85	81	78	90	84	81	78	84	80	78	78	83	80	78	78	82	79	77	77	76	76	76	76
10	89	83	79	76	88	82	79	76	82	78	76	76	81	78	76	76	80	78	76	76	75	75	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	793848
5°	788956
10°	508005
15°	163451
20°	43579
25°	22320
30°	15952
35°	13853
40°	11593
45°	9768
50°	8443
55°	6021
60°	3947
65°	2335
70°	1443
75°	1906
80°	0
85°	0



TEST NUMBER: G2-1802-569-39

CATALOG NUMBER: 203-SS-8LED4010-12-CS-OSL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.4	45.5
10°-20°	103.9	35.7
20°-30°	20.8	7.1
30°-40°	14.2	4.9
40°-50°	11.1	3.8
50°-60°	6.3	2.2
60°-70°	1.8	0.6
70°-80°	0.7	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	257.1	88.3
0°-40°	271.2	93.2
0°-60°	288.6	99.1
0°-90°	291.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	291.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1609	
5°	1593	132
15°	320	104
25°	41	21
35°	23	14
45°	14	11
55°	7	6
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: G2-1802-569-39
CATALOG NUMBER: 203-SS-8LED4010-12-CS-OSL

CANDELA DISTRIBUTION (FULL):

	0°
0°	1609
1°	1615
2°	1631
3°	1641
4°	1631
5°	1593
6°	1521
7°	1419
8°	1295
9°	1155
10°	1014
12.5°	645
15°	320
17.5°	148
20°	83
22.5°	56
25°	41
27.5°	33
30°	28
32.5°	25
35°	23
37.5°	20
40°	18
42.5°	16
45°	14
47.5°	13
50°	11
52.5°	9
55°	7
57.5°	5
60°	4
62.5°	2
65°	2
67.5°	1
70°	1
72.5°	1
75°	1
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)