

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P827944

Luminaire Tested: **OHBL-12HE-A-UNV-L935-CD-UPL18**

Issue Date: 5/3/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P827944  
REPORT IS A COMBINATION OF REPORTS P826143 AND G3-2310-221-8  
Test Lab: INNOVATION CENTER  
Issue Date: 5/3/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: OHBL-12HE-A-UNV-L935-CD-UPL18  
Description:  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1491.6 lumens  
Efficiency: N/A  
Efficacy: 121.3 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular w/ Sides (W: 3.78' x L: 1.67' x H: 0.17')  
CIE Type: Indirect

Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P827944

CATALOG NUMBER: OHBL-12HE-A-UNV-L935-CD-UPL18

### Luminous Intensity Polar Plot





TEST NUMBER: P827944

CATALOG NUMBER: OHBL-12HE-A-UNV-L935-CD-UPL18

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0																
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	9	9	9	9	0																
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0																
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0																
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0																
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0																
6	55	44	36	31	47	38	31	27	26	22	19	15	13	11	5	4	4	4	4	4	0																
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0																
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0																
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	2	2	2	2	0																
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P827944

CATALOG NUMBER: OHBL-12HE-A-UNV-L935-CD-UPL18

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.7	0.3
90°-100°	142.7	9.6
100°-110°	495.5	33.2
110°-120°	425.7	28.5
120°-130°	204.5	13.7
130°-140°	102.1	6.8
140°-150°	59.3	4.0
150°-160°	34.6	2.3
160°-170°	17.9	1.2
170°-180°	5.5	0.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.7	0.3
90°-120°	1063.9	71.3
90°-150°	1429.8	95.9
90°-180°	1488.0	99.8
0°-180°	1491.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	21	28	38	42	2
95°	32	68	108	139	159	100
105°	618	612	522	368	339	586
115°	428	432	432	427	426	431
125°	208	218	224	223	222	196
135°	123	126	130	132	132	98
145°	90	92	94	95	95	57
155°	72	73	74	75	75	34
165°	62	62	62	63	63	18
175°	56	56	57	57	57	5
180°	56	56	56	56	56	



TEST NUMBER: P827944

CATALOG NUMBER: OHBL-12HE-A-UNV-L935-CD-UPL18

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.3	20.8	28.3	37.5	41.7
92.5°	10.8	27.5	45.8	63.3	70.0
95°	31.7	68.3	107.5	139.2	159.2
97.5°	162.5	177.5	198.3	235.0	248.3
100°	335.0	351.7	295.0	309.2	314.2
102.5°	524.2	523.3	378.3	341.7	336.7
105°	617.5	611.7	521.7	367.5	339.2



TEST NUMBER: P827944

CATALOG NUMBER: OHBL-12HE-A-UNV-L935-CD-UPL18

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	501.7	505.0	495.0	481.7	460.8
115°	427.5	432.5	431.7	426.7	425.8
117.5°	364.2	366.7	368.3	366.7	367.5
120°	304.2	310.0	313.3	310.8	309.2
122.5°	254.2	261.7	265.8	263.3	261.7
125°	208.3	218.3	224.2	223.3	221.7
127.5°	176.7	184.2	191.7	190.8	189.2
130°	153.3	159.2	164.2	165.0	165.8
132.5°	137.5	140.0	145.0	145.8	147.5
135°	123.3	125.8	130.0	131.7	132.5
137.5°	112.5	115.0	118.3	120.0	120.8
140°	103.3	105.8	108.3	110.0	110.8
142.5°	95.8	98.3	100.8	101.7	102.5
145°	90.0	91.7	94.2	95.0	95.0
147.5°	84.2	85.8	87.5	89.2	89.2
150°	79.2	80.8	82.5	83.3	84.2
152.5°	75.8	76.7	78.3	79.2	79.2
155°	71.7	73.3	74.2	75.0	75.0
157.5°	69.2	70.0	70.8	71.7	71.7
160°	66.7	66.7	67.5	68.3	68.3
162.5°	64.2	64.2	65.0	65.8	65.8
165°	61.7	62.5	62.5	63.3	63.3
167.5°	60.0	60.0	60.8	60.8	61.7
170°	58.3	58.3	59.2	59.2	59.2
172.5°	56.7	57.5	57.5	57.5	57.5
175°	55.8	55.8	56.7	56.7	56.7
177.5°	55.0	55.8	55.8	55.8	55.8
180°	55.8	55.8	55.8	55.8	55.8



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	623.3	623.3	575.0	446.7	374.2
110°	570.8	577.5	552.5	502.5	445.0



(END OF REPORT)