

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P827678

Luminaire Tested: **OHBL-15HE-W-UNV-L930-CD-UPL24**

Issue Date: 5/3/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P827678  
REPORT IS A COMBINATION OF REPORTS P826220 AND G3-2310-221-6  
Test Lab: INNOVATION CENTER  
Issue Date: 5/3/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: OHBL-15HE-W-UNV-L930-CD-UPL24  
Description:  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1956.4 lumens  
Efficiency: N/A  
Efficacy: 112.4 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular w/ Sides (W: 3.78' x L: 1.67' x H: 0.17')  
CIE Type: Indirect  
  
Input Watts (W): 17.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P827678

CATALOG NUMBER: OHBL-15HE-W-UNV-L930-CD-UPL24

### Luminous Intensity Polar Plot





TEST NUMBER: P827678

CATALOG NUMBER: OHBL-15HE-W-UNV-L930-CD-UPL24

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0																
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	9	9	9	9	0																
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0																
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0																
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0																
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0																
6	55	44	36	31	47	38	31	27	26	22	19	15	13	11	5	4	4	4	4	4	0																
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0																
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0																
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	2	2	2	2	0																
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P827678

CATALOG NUMBER: OHBL-15HE-W-UNV-L930-CD-UPL24

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	5.0	0.3
90°-100°	187.4	9.6
100°-110°	650.6	33.3
110°-120°	558.1	28.5
120°-130°	267.8	13.7
130°-140°	134.0	6.8
140°-150°	77.7	4.0
150°-160°	45.3	2.3
160°-170°	23.5	1.2
170°-180°	7.1	0.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	5.0	0.3
90°-120°	1396.2	71.4
90°-150°	1875.5	95.9
90°-180°	1951.0	99.7
0°-180°	1956.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	4	28	38	50	56	3
95°	43	90	139	184	209	133
105°	811	802	682	486	446	769
115°	559	565	565	563	559	564
125°	273	288	293	293	290	256
135°	162	165	171	172	174	128
145°	117	120	123	124	124	75
155°	94	95	97	98	98	44
165°	81	82	82	82	82	23
175°	73	74	74	74	74	7
180°	73	73	73	73	73	



TEST NUMBER: P827678

CATALOG NUMBER: OHBL-15HE-W-UNV-L930-CD-UPL24

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	4.0	27.5	38.0	50.1	55.8
92.5°	13.7	36.4	58.2	82.4	93.0
95°	42.8	89.7	139.0	184.3	208.6
97.5°	217.4	235.2	253.0	306.4	333.0
100°	446.2	473.7	382.3	404.2	411.4
102.5°	689.5	685.5	499.6	447.8	441.4
105°	810.8	801.9	682.2	485.8	446.2



TEST NUMBER: P827678

CATALOG NUMBER: OHBL-15HE-W-UNV-L930-CD-UPL24

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	653.1	662.8	649.9	631.3	605.4
115°	559.4	565.0	565.0	563.4	558.6
117.5°	478.5	479.3	482.6	481.8	482.6
120°	396.1	405.0	412.2	408.2	403.4
122.5°	332.2	341.9	346.8	345.2	340.3
125°	273.2	287.8	293.4	292.6	290.2
127.5°	231.2	241.7	249.8	250.6	249.8
130°	201.3	207.7	215.8	216.6	217.4
132.5°	178.6	184.3	190.0	193.2	192.4
135°	161.7	164.9	170.6	172.2	173.8
137.5°	147.9	150.4	155.2	157.6	157.6
140°	135.8	139.0	143.1	144.7	145.5
142.5°	125.3	128.5	131.8	133.4	133.4
145°	117.2	120.4	122.9	123.7	124.5
147.5°	109.9	113.2	114.8	116.4	116.4
150°	104.3	105.9	108.3	109.1	109.9
152.5°	98.6	100.2	102.7	103.5	103.5
155°	93.8	95.4	97.0	97.8	97.8
157.5°	89.7	91.3	93.0	93.8	93.8
160°	86.5	87.3	88.9	89.7	89.7
162.5°	83.3	84.1	84.9	85.7	85.7
165°	80.8	81.6	82.4	82.4	82.4
167.5°	78.4	78.4	79.2	80.0	80.0
170°	76.0	76.8	76.8	77.6	77.6
172.5°	74.4	75.2	75.2	75.2	76.0
175°	72.8	73.6	73.6	74.4	74.4
177.5°	72.8	72.8	72.8	72.8	72.8
180°	72.8	72.8	72.8	72.8	72.8



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	814.0	817.2	754.2	589.3	490.7
110°	750.9	758.2	721.8	659.6	580.4



(END OF REPORT)